

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245930

Luminaire Tested: P3A02R709024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245930
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R709024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 154.0 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245930

CATALOG NUMBER: P3A02R709024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1245930

CATALOG NUMBER: P3A02R709024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	88	83		98	92	87	83		89	85	81		87	83	80		84	81	79
4	95	86	80	76		93	85	80	75		83	78	74		81	77	73		79	76	73
5	89	80	74	69		88	79	73	69		78	72	68		76	71	68		74	70	67
6	85	75	68	64		83	74	68	64		73	67	63		71	66	63		70	65	62
7	80	70	64	59		79	69	63	59		68	62	58		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	62	55	51		71	61	55	51		60	55	51		59	54	51		58	54	50
10	69	58	52	48		67	58	52	48		57	51	48		56	51	48		55	51	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36116
5°	35461
10°	33444
15°	30352
20°	26532
25°	22380
30°	18332
35°	14214
40°	10191
45°	6450
50°	3207
55°	1950
60°	1710
65°	1557
70°	1346
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6450 cd/sqm

TEST NUMBER: P1245930

CATALOG NUMBER: P3A02R709024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.0	9.8
10°-20°	37.2	24.2
20°-30°	42.4	27.5
30°-40°	33.1	21.5
40°-50°	16.3	10.6
50°-60°	5.0	3.2
60°-70°	3.0	1.9
70°-80°	1.6	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.6	61.4
0°-40°	127.7	82.9
0°-60°	149.0	96.8
0°-90°	154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	154.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	165	
5°	161	15
15°	134	37
25°	92	42
35°	53	33
45°	21	16
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1245930

CATALOG NUMBER: P3A02R709024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	164.7
2.5°	163.9
5°	161.1
7.5°	156.6
10°	150.2
12.5°	142.7
15°	133.7
17.5°	124.0
20°	113.7
22.5°	103.0
25°	92.5
27.5°	82.3
30°	72.4
32.5°	62.6
35°	53.1
37.5°	44.1
40°	35.6
42.5°	27.6
45°	20.8
47.5°	14.6
50°	9.4
52.5°	6.2
55°	5.1
57.5°	4.5
60°	3.9
62.5°	3.4
65°	3.0
67.5°	2.6
70°	2.1
72.5°	1.7
75°	1.5
77.5°	1.3
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)