

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246078

Luminaire Tested: P3A05R259024DE010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246078
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R259024DE010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 354.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246078

CATALOG NUMBER: P3A05R259024DE010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1246078

CATALOG NUMBER: P3A05R259024DE010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84138
5°	82126
10°	76106
15°	67787
20°	58245
25°	49503
30°	40766
35°	31748
40°	22843
45°	14482
50°	8563
55°	5887
60°	5394
65°	5033
70°	4552
75°	4151
80°	3915
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14482 cd/sqm

TEST NUMBER: P1246078

CATALOG NUMBER: P3A05R259024DE010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.6	9.8
10°-20°	82.9	23.4
20°-30°	93.6	26.5
30°-40°	74.1	20.9
40°-50°	37.4	10.6
50°-60°	15.0	4.2
60°-70°	9.6	2.7
70°-80°	5.3	1.5
80°-90°	1.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.1	59.6
0°-40°	285.2	80.6
0°-60°	337.6	95.4
0°-90°	354.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	354.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	373	35
15°	299	83
25°	205	94
35°	119	74
45°	47	37
55°	15	15
65°	10	10
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1246078

CATALOG NUMBER: P3A05R259024DE010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	383.7
1°	383.7
2°	382.4
3°	380.2
4°	377.1
5°	373.1
6°	368.2
7°	362.5
8°	356.3
9°	349.3
10°	341.8
11°	333.4
12°	325.5
13°	316.2
14°	307.4
15°	298.6
17.5°	273.9
20°	249.6
22.5°	226.7
25°	204.6
27.5°	183.0
30°	161.0
32.5°	140.2
35°	118.6
37.5°	98.8
40°	79.8
42.5°	62.2
45°	46.7
47.5°	34.8
50°	25.1
52.5°	19.0
55°	15.4
57.5°	14.1
60°	12.3
62.5°	11.0
65°	9.7
67.5°	8.4
70°	7.1
72.5°	6.2
75°	4.9
77.5°	4.0
80°	3.1
82.5°	2.2
85°	1.3
87.5°	0.4



TEST NUMBER: P1246078

CATALOG NUMBER: P3A05R259024DE010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)