

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246128

Luminaire Tested: P3A05R359024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R359024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 31.5 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246128

CATALOG NUMBER: P3A05R359024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246128

CATALOG NUMBER: P3A05R359024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	106	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77
8	85	77	72	69	84	77	72	69	76	71	68		75	71	68		74
9	82	74	69	66	81	74	69	65	73	68	65		72	68	65		71
10	79	71	66	63	78	71	66	63	70	66	63		69	65	62		69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114486
5°	110037
10°	95879
15°	73440
20°	49121
25°	29736
30°	17066
35°	9530
40°	5067
45°	2605
50°	1262
55°	994
60°	965
65°	778
70°	833
75°	763
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2605 cd/sqm

TEST NUMBER: P1246128

CATALOG NUMBER: P3A05R359024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	20.0
10°-20°	88.1	38.8
20°-30°	57.7	25.4
30°-40°	23.4	10.3
40°-50°	7.0	3.1
50°-60°	2.4	1.1
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	191.3	84.3
0°-40°	214.7	94.6
0°-60°	224.2	98.8
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	522	
5°	500	45
15°	324	88
25°	123	58
35°	36	23
45°	8	7
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246128

CATALOG NUMBER: P3A05R359024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	522.1
1°	521.2
2°	518.9
3°	514.1
4°	508.5
5°	499.9
6°	489.1
7°	477.0
8°	463.4
9°	447.8
10°	430.6
11°	411.3
12°	391.3
13°	368.8
14°	347.4
15°	323.5
17.5°	265.4
20°	210.5
22.5°	161.9
25°	122.9
27.5°	91.6
30°	67.4
32.5°	49.4
35°	35.6
37.5°	25.3
40°	17.7
42.5°	12.3
45°	8.4
47.5°	5.6
50°	3.7
52.5°	2.8
55°	2.6
57.5°	2.4
60°	2.2
62.5°	1.9
65°	1.5
67.5°	1.3
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.6
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1246128

CATALOG NUMBER: P3A05R359024DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)