

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246207

Luminaire Tested: P3A05R509024DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R509024DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 605.0 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246207
CATALOG NUMBER: P3A05R509024DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1246207
 CATALOG NUMBER: P3A05R509024DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.2	14.6
10°-20°	223.1	36.9
20°-30°	223.4	36.9
30°-40°	62.8	10.4
40°-50°	3.8	0.6
50°-60°	1.4	0.2
60°-70°	1.1	0.2
70°-80°	0.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.7	88.4
0°-40°	597.6	98.8
0°-60°	602.8	99.6
0°-90°	605.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	605.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	961	
5°	940	88
15°	803	223
25°	509	223
35°	80	63
45°	2	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1246207

CATALOG NUMBER: P3A05R509024DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	960.9
2.5°	956.0
5°	940.1
7.5°	918.4
10°	892.3
12.5°	853.0
15°	802.6
17.5°	744.7
20°	688.5
22.5°	618.6
25°	509.0
27.5°	379.0
30°	264.4
32.5°	159.6
35°	80.5
37.5°	38.0
40°	17.7
42.5°	6.6
45°	2.2
47.5°	1.8
50°	1.8
52.5°	1.8
55°	1.8
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)