

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426137

Luminaire Tested: P3A05RH9024DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05RH9024DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 2400K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 212.0 lumens
Efficiency: N/A
Efficacy: 29.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426137

CATALOG NUMBER: P3A05RH9024DE010 E3HY1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1426137

CATALOG NUMBER: P3A05RH9024DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93		96	94	91		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	82
4	99	92	86	82	97	90	86	82	88	84	81		86	83	80		84	81	79	78
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102229
5°	93660
10°	81851
15°	71805
20°	36333
25°	18098
30°	16357
35°	12421
40°	8731
45°	5892
50°	3787
55°	2523
60°	1754
65°	1401
70°	833
75°	763
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5892 cd/sqm

TEST NUMBER: P1426137

CATALOG NUMBER: P3A05RH9024DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	18.3
10°-20°	80.1	37.8
20°-30°	39.1	18.4
30°-40°	29.2	13.8
40°-50°	15.0	7.1
50°-60°	6.2	2.9
60°-70°	2.5	1.2
70°-80°	0.9	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.0	74.5
0°-40°	187.1	88.3
0°-60°	208.4	98.3
0°-90°	212.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	212.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	466	
5°	426	39
15°	316	80
25°	75	39
35°	46	29
45°	19	15
55°	7	6
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1426137

CATALOG NUMBER: P3A05RH9024DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	466.2
2.5°	455.6
5°	425.5
7.5°	393.2
10°	367.6
12.5°	348.6
15°	316.3
17.5°	246.8
20°	155.7
22.5°	92.4
25°	74.8
27.5°	69.0
30°	64.6
32.5°	56.6
35°	46.4
37.5°	38.0
40°	30.5
42.5°	24.3
45°	19.0
47.5°	14.6
50°	11.1
52.5°	8.4
55°	6.6
57.5°	5.3
60°	4.0
62.5°	3.1
65°	2.7
67.5°	1.8
70°	1.3
72.5°	1.3
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)