

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251186

Luminaire Tested: P3A05R309030DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05R309030DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 408.0 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251186

CATALOG NUMBER: P3A05R309030DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1251186

CATALOG NUMBER: P3A05R309030DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	96	92		104	99	94	91		95	92	89		92	89	87		89	87	85
3	100	92	87	82		98	91	86	82		88	84	80		86	82	79		84	80	78
4	94	86	79	74		92	84	79	74		82	77	73		80	76	72		78	74	71
5	89	79	73	68		87	78	72	68		76	71	67		75	70	66		73	69	66
6	84	74	67	62		82	73	67	62		71	66	62		70	65	61		69	64	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	54		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	61	54	50		70	60	54	50		59	54	50		58	53	50		57	53	49
10	68	57	51	47		67	57	51	47		56	50	47		55	50	46		54	50	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96396
5°	94233
10°	87618
15°	77980
20°	67066
25°	56810
30°	47146
35°	36995
40°	26507
45°	17397
50°	9893
55°	6499
60°	6140
65°	5707
70°	5129
75°	4660
80°	4420
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17397 cd/sqm

TEST NUMBER: P1251186

CATALOG NUMBER: P3A05R309030DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.7	9.7
10°-20°	95.5	23.4
20°-30°	107.6	26.4
30°-40°	85.9	21.1
40°-50°	44.2	10.8
50°-60°	16.6	4.1
60°-70°	10.9	2.7
70°-80°	5.9	1.4
80°-90°	1.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	242.8	59.5
0°-40°	328.8	80.6
0°-60°	389.5	95.5
0°-90°	408.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	408.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	440	
5°	428	40
15°	344	95
25°	235	108
35°	138	86
45°	56	44
55°	17	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1251186

CATALOG NUMBER: P3A05R309030DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	439.6
1°	439.6
2°	438.1
3°	435.6
4°	432.1
5°	428.1
6°	423.1
7°	416.5
8°	409.5
9°	401.5
10°	393.5
11°	384.5
12°	375.0
13°	365.0
14°	354.5
15°	343.5
17.5°	315.4
20°	287.4
22.5°	260.3
25°	234.8
27.5°	209.8
30°	186.2
32.5°	162.2
35°	138.2
37.5°	114.7
40°	92.6
42.5°	73.1
45°	56.1
47.5°	41.6
50°	29.0
52.5°	20.5
55°	17.0
57.5°	15.5
60°	14.0
62.5°	12.5
65°	11.0
67.5°	9.5
70°	8.0
72.5°	6.5
75°	5.5
77.5°	4.5
80°	3.5
82.5°	2.5
85°	1.5
87.5°	0.5



TEST NUMBER: P1251186

CATALOG NUMBER: P3A05R309030DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2504-409-28

Test Date: 05/16/2025

Luminaire Tested: LD3A09R159030D010 E3D1H

Data in this report applies to families of products including LD3A

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2504-409-28
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/06/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A09R159030D010 E3D1H**
 Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI LEDS, E3D1H TRIM

Spectral Parameters

CCT (K): 3032
 CIE u' : 0.2493
 CIE v' : 0.5211
 Duv: 0.0003
 CIE x: 0.4351
 CIE y: 0.4042
 CIE z: 0.1608
 Peak Wavelength (nm): 615
 Dominant Wavelength (nm): 582
 Purity: 51.90029
 R_f: 91.6
 R_g: 98.2

CRI (Ra): 92.8
 R1: 93.5
 R2: 97.3
 R3: 98.7
 R4: 93.9
 R5: 93.6
 R6: 96.7
 R7: 90.3
 R8: 78.4
 R9: 51.3
 R10: 93.2
 R11: 96.4
 R12: 82.1
 R13: 94.8
 R14: 99.6
 R15: 87.6



Test Conditions

Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2504-409-28

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2504-409-28

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2504-409-28

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	285	NR	620	993	NR	750	55	NR	880	1	NR
365	0	NR	495	338	NR	625	970	NR	755	47	NR	885	1	NR
370	0	NR	500	392	NR	630	942	NR	760	41	NR	890	1	NR
375	0	NR	505	440	NR	635	902	NR	765	35	NR	895	1	NR
380	0	NR	510	478	NR	640	855	NR	770	30	NR	900	1	NR
385	0	NR	515	505	NR	645	800	NR	775	26	NR	905	1	NR
390	0	NR	520	524	NR	650	743	NR	780	22	NR	910	0	NR
395	1	NR	525	539	NR	655	682	NR	785	19	NR	915	0	NR
400	2	NR	530	554	NR	660	621	NR	790	16	NR	920	0	NR
405	3	NR	535	565	NR	665	563	NR	795	14	NR	925	1	NR
410	5	NR	540	581	NR	670	505	NR	800	12	NR	930	0	NR
415	10	NR	545	593	NR	675	451	NR	805	10	NR	935	0	NR
420	17	NR	550	606	NR	680	401	NR	810	9	NR	940	0	NR
425	32	NR	555	623	NR	685	356	NR	815	8	NR	945	0	NR
430	57	NR	560	645	NR	690	313	NR	820	7	NR	950	0	NR
435	103	NR	565	667	NR	695	274	NR	825	6	NR	955	0	NR
440	175	NR	570	699	NR	700	238	NR	830	5	NR	960	0	NR
445	287	NR	575	732	NR	705	208	NR	835	4	NR	965	0	NR
450	460	NR	580	774	NR	710	180	NR	840	4	NR	970	0	NR
455	550	NR	585	816	NR	715	157	NR	845	3	NR	975	0	NR
460	423	NR	590	862	NR	720	136	NR	850	3	NR	980	0	NR
465	309	NR	595	907	NR	725	117	NR	855	2	NR	985	0	NR
470	269	NR	600	943	NR	730	100	NR	860	2	NR	990	0	NR
475	229	NR	605	974	NR	735	86	NR	865	2	NR	995	0	NR
480	214	NR	610	991	NR	740	72	NR	870	2	NR	1000	0	NR
485	241	NR	615	1000	NR	745	62	NR	875	1	NR			

REPORT NUMBER: SP1-2504-409-28

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	285	NR	620	993	NR	750	55	NR	880	1	NR
365	0	NR	495	338	NR	625	970	NR	755	47	NR	885	1	NR
370	0	NR	500	392	NR	630	942	NR	760	41	NR	890	1	NR
375	0	NR	505	440	NR	635	902	NR	765	35	NR	895	1	NR
380	0	NR	510	478	NR	640	855	NR	770	30	NR	900	1	NR
385	0	NR	515	505	NR	645	800	NR	775	26	NR	905	1	NR
390	0	NR	520	524	NR	650	743	NR	780	22	NR	910	0	NR
395	1	NR	525	539	NR	655	682	NR	785	19	NR	915	0	NR
400	2	NR	530	554	NR	660	621	NR	790	16	NR	920	0	NR
405	3	NR	535	565	NR	665	563	NR	795	14	NR	925	1	NR
410	5	NR	540	581	NR	670	505	NR	800	12	NR	930	0	NR
415	10	NR	545	593	NR	675	451	NR	805	10	NR	935	0	NR
420	17	NR	550	606	NR	680	401	NR	810	9	NR	940	0	NR
425	32	NR	555	623	NR	685	356	NR	815	8	NR	945	0	NR
430	57	NR	560	645	NR	690	313	NR	820	7	NR	950	0	NR
435	103	NR	565	667	NR	695	274	NR	825	6	NR	955	0	NR
440	175	NR	570	699	NR	700	238	NR	830	5	NR	960	0	NR
445	287	NR	575	732	NR	705	208	NR	835	4	NR	965	0	NR
450	460	NR	580	774	NR	710	180	NR	840	4	NR	970	0	NR
455	550	NR	585	816	NR	715	157	NR	845	3	NR	975	0	NR
460	423	NR	590	862	NR	720	136	NR	850	3	NR	980	0	NR
465	309	NR	595	907	NR	725	117	NR	855	2	NR	985	0	NR
470	269	NR	600	943	NR	730	100	NR	860	2	NR	990	0	NR
475	229	NR	605	974	NR	735	86	NR	865	2	NR	995	0	NR
480	214	NR	610	991	NR	740	72	NR	870	2	NR	1000	0	NR
485	241	NR	615	1000	NR	745	62	NR	875	1	NR			

REPORT NUMBER: SP1-2504-409-28

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.84

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	285	NR	620	993	NR	750	55	NR	880	1	NR
365	0	NR	495	338	NR	625	970	NR	755	47	NR	885	1	NR
370	0	NR	500	392	NR	630	942	NR	760	41	NR	890	1	NR
375	0	NR	505	440	NR	635	902	NR	765	35	NR	895	1	NR
380	0	NR	510	478	NR	640	855	NR	770	30	NR	900	1	NR
385	0	NR	515	505	NR	645	800	NR	775	26	NR	905	1	NR
390	0	NR	520	524	NR	650	743	NR	780	22	NR	910	0	NR
395	1	NR	525	539	NR	655	682	NR	785	19	NR	915	0	NR
400	2	NR	530	554	NR	660	621	NR	790	16	NR	920	0	NR
405	3	NR	535	565	NR	665	563	NR	795	14	NR	925	1	NR
410	5	NR	540	581	NR	670	505	NR	800	12	NR	930	0	NR
415	10	NR	545	593	NR	675	451	NR	805	10	NR	935	0	NR
420	17	NR	550	606	NR	680	401	NR	810	9	NR	940	0	NR
425	32	NR	555	623	NR	685	356	NR	815	8	NR	945	0	NR
430	57	NR	560	645	NR	690	313	NR	820	7	NR	950	0	NR
435	103	NR	565	667	NR	695	274	NR	825	6	NR	955	0	NR
440	175	NR	570	699	NR	700	238	NR	830	5	NR	960	0	NR
445	287	NR	575	732	NR	705	208	NR	835	4	NR	965	0	NR
450	460	NR	580	774	NR	710	180	NR	840	4	NR	970	0	NR
455	550	NR	585	816	NR	715	157	NR	845	3	NR	975	0	NR
460	423	NR	590	862	NR	720	136	NR	850	3	NR	980	0	NR
465	309	NR	595	907	NR	725	117	NR	855	2	NR	985	0	NR
470	269	NR	600	943	NR	730	100	NR	860	2	NR	990	0	NR
475	229	NR	605	974	NR	735	86	NR	865	2	NR	995	0	NR
480	214	NR	610	991	NR	740	72	NR	870	2	NR	1000	0	NR
485	241	NR	615	1000	NR	745	62	NR	875	1	NR			

REPORT NUMBER: SP1-2504-409-28

TM-30-18

Summary

$R_f = 91.6$
 $R_g = 98.2$
 $\text{CIE } R_a = 92.8$
 $R_9 = 51.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 96	CES51 = 97	CES76 = 92
CES02 = 63	CES27 = 91	CES52 = 99	CES77 = 88
CES03 = 32	CES28 = 98	CES53 = 98	CES78 = 88
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 91
CES05 = 50	CES30 = 90	CES55 = 91	CES80 = 92
CES06 = 51	CES31 = 97	CES56 = 94	CES81 = 78
CES07 = 43	CES32 = 93	CES57 = 93	CES82 = 96
CES08 = 42	CES33 = 97	CES58 = 94	CES83 = 95
CES09 = 29	CES34 = 97	CES59 = 97	CES84 = 95
CES10 = 76	CES35 = 98	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 82	CES61 = 93	CES86 = 79
CES12 = 65	CES37 = 98	CES62 = 87	CES87 = 91
CES13 = 44	CES38 = 86	CES63 = 94	CES88 = 95
CES14 = 74	CES39 = 98	CES64 = 92	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 89	CES90 = 94
CES16 = 48	CES41 = 96	CES66 = 90	CES91 = 77
CES17 = 50	CES42 = 97	CES67 = 89	CES92 = 76
CES18 = 57	CES43 = 96	CES68 = 91	CES93 = 86
CES19 = 72	CES44 = 99	CES69 = 92	CES94 = 76
CES20 = 67	CES45 = 99	CES70 = 89	CES95 = 83
CES21 = 86	CES46 = 96	CES71 = 85	CES96 = 91
CES22 = 79	CES47 = 93	CES72 = 95	CES97 = 96
CES23 = 92	CES48 = 89	CES73 = 85	CES98 = 93
CES24 = 90	CES49 = 97	CES74 = 90	CES99 = 89
CES25 = 72	CES50 = 97	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)