

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246644

Luminaire Tested: P3A09R609024DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R609024DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 834.9 lumens
Efficiency: N/A
Efficacy: 75.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246644

CATALOG NUMBER: P3A09R609024DE010 E3CD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1246644

CATALOG NUMBER: P3A09R609024DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	100	98		97	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	70	68
7	84	75	69	64		82	74	68	64		73	68	64		71	67	64		70	66	63
8	80	70	64	60		79	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	56	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199392
5°	191481
10°	197146
15°	199683
20°	176322
25°	148605
30°	120525
35°	78487
40°	36039
45°	13831
50°	4640
55°	1223
60°	1140
65°	986
70°	833
75°	1101
80°	758
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13831 cd/sqm

TEST NUMBER: P1246644

CATALOG NUMBER: P3A09R609024DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.7	10.0
10°-20°	240.9	28.8
20°-30°	281.0	33.7
30°-40°	181.3	21.7
40°-50°	40.6	4.9
50°-60°	4.1	0.5
60°-70°	1.9	0.2
70°-80°	1.1	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	605.6	72.5
0°-40°	786.9	94.2
0°-60°	831.5	99.6
0°-90°	834.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	834.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	909	
5°	870	84
15°	880	241
25°	614	281
35°	293	181
45°	45	41
55°	3	4
65°	2	2
75°	1	1
85°	1	0
90°	0	

TEST NUMBER: P1246644

CATALOG NUMBER: P3A09R609024DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	909.3
2.5°	894.5
5°	869.9
7.5°	868.6
10°	885.4
12.5°	896.4
15°	879.6
17.5°	829.2
20°	755.6
22.5°	678.8
25°	614.2
27.5°	550.9
30°	476.0
32.5°	388.1
35°	293.2
37.5°	200.2
40°	125.9
42.5°	75.6
45°	44.6
47.5°	25.8
50°	13.6
52.5°	4.5
55°	3.2
57.5°	2.6
60°	2.6
62.5°	1.9
65°	1.9
67.5°	1.9
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)