

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246692

Luminaire Tested: P3A09R659024DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1246692  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R659024DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 447.0 lumens  
Efficiency: N/A  
Efficacy: 40.3 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1246692  
CATALOG NUMBER: P3A09R659024DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1246692  
 CATALOG NUMBER: P3A09R659024DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113609
5°	110786
10°	103182
15°	92464
20°	79854
25°	66415
30°	52388
35°	38815
40°	26736
45°	16591
50°	9006
55°	5658
60°	4824
65°	4358
70°	3719
75°	3304
80°	3283
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 16591 cd/sqm



TEST NUMBER: P1246692  
 CATALOG NUMBER: P3A09R659024DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.8	10.5
10°-20°	113.2	25.3
20°-30°	125.2	28.0
30°-40°	90.9	20.3
40°-50°	42.6	9.5
50°-60°	14.3	3.2
60°-70°	8.3	1.9
70°-80°	4.4	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.1	63.8
0°-40°	376.0	84.1
0°-60°	433.0	96.9
0°-90°	447.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	447.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	518	
5°	503	47
15°	407	113
25°	274	125
35°	145	91
45°	54	43
55°	15	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1246692  
CATALOG NUMBER: P3A09R659024DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	518.1
2.5°	514.9
5°	503.3
7.5°	485.9
10°	463.4
12.5°	436.9
15°	407.3
17.5°	375.1
20°	342.2
22.5°	308.1
25°	274.5
27.5°	240.4
30°	206.9
32.5°	174.6
35°	145.0
37.5°	117.9
40°	93.4
42.5°	71.5
45°	53.5
47.5°	38.7
50°	26.4
52.5°	18.0
55°	14.8
57.5°	12.9
60°	11.0
62.5°	9.7
65°	8.4
67.5°	7.1
70°	5.8
72.5°	5.2
75°	3.9
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)