

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255674

Luminaire Tested: P3A24R209035D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R209035D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2558.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255674

CATALOG NUMBER: P3A24R209035D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1255674

CATALOG NUMBER: P3A24R209035D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	114	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	105	103		104	102	101		101	100	98		99	98	96
3	109	105	102	99		107	104	101	98		101	99	97		99	97	95		97	95	94
4	106	101	98	95		105	100	97	95		99	96	94		97	95	93		95	93	92
5	104	98	95	92		102	98	94	92		96	93	91		95	92	90		93	91	90
6	101	96	92	89		100	95	92	89		94	91	89		93	90	88		92	89	88
7	99	93	90	87		98	93	89	87		92	89	86		91	88	86		90	87	86
8	97	91	87	85		96	91	87	85		90	87	85		89	86	84		88	86	84
9	95	89	85	83		94	89	85	83		88	85	83		87	84	83		87	84	82
10	93	87	84	81		92	87	83	81		86	83	81		86	83	81		85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3880281
5°	3267018
10°	2040555
15°	762887
20°	261869
25°	109143
30°	51400
35°	23022
40°	10878
45°	5582
50°	2047
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5582 cd/sqm

TEST NUMBER: P1255674

CATALOG NUMBER: P3A24R209035D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1234.3	48.3
10°-20°	1016.7	39.7
20°-30°	231.0	9.0
30°-40°	58.8	2.3
40°-50°	14.8	0.6
50°-60°	1.9	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2481.9	97.0
0°-40°	2540.7	99.3
0°-60°	2557.4	100.0
0°-90°	2558.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2558.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17696	
5°	14842	###
15°	3360	1017
25°	451	231
35°	86	59
45°	18	15
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1255674

CATALOG NUMBER: P3A24R209035D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	17695.5
1°	17545.5
2°	17103.4
3°	16469.3
4°	15691.2
5°	14842.1
6°	13896.0
7°	12851.8
8°	11633.6
9°	10426.5
10°	9164.3
11°	7821.1
12°	6479.9
13°	5343.8
14°	4257.6
15°	3360.5
16°	2652.4
17°	2092.3
18°	1681.2
19°	1367.2
20°	1122.2
21°	938.1
22°	783.1
23°	651.1
24°	543.1
25°	451.1
27.5°	295.0
30°	203.0
32.5°	125.0
35°	86.0
37.5°	55.0
40°	38.0
42.5°	26.0
45°	18.0
47.5°	12.0
50°	6.0
52.5°	3.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1255674

CATALOG NUMBER: P3A24R209035D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)