

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255760

Luminaire Tested: P3A24R359035D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R359035D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2591.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255760

CATALOG NUMBER: P3A24R359035D010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1255760

CATALOG NUMBER: P3A24R359035D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	103	100	102	100	98		99	98	96		97
3	107	102	98	95	105	101	97	95	98	96	93		96	94	92		94
4	104	98	94	91	102	97	93	90	95	92	89		93	90	88		91
5	100	94	90	87	99	93	89	86	92	88	86		90	87	85		89
6	97	91	86	83	96	90	86	83	89	85	82		87	84	82		86
7	94	87	83	80	93	87	83	80	86	82	79		85	81	79		84
8	91	84	80	77	90	84	80	77	83	79	77		82	79	76		81
9	89	82	77	74	88	81	77	74	80	77	74		80	76	74		79
10	86	79	75	72	85	79	75	72	78	74	72		77	74	72		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1689514
5°	1655091
10°	1539740
15°	1128860
20°	578040
25°	208343
30°	81126
35°	28402
40°	11679
45°	3163
50°	2797
55°	3135
60°	2675
65°	2127
70°	2629
75°	3474
80°	2526
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 3474 cd/sqm

TEST NUMBER: P1255760

CATALOG NUMBER: P3A24R359035D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	701.0	27.1
10°-20°	1315.2	50.8
20°-30°	465.6	18.0
30°-40°	81.5	3.1
40°-50°	11.9	0.5
50°-60°	6.6	0.3
60°-70°	4.8	0.2
70°-80°	3.5	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2481.8	95.8
0°-40°	2563.3	98.9
0°-60°	2581.9	99.6
0°-90°	2591.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2591.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7705	
5°	7519	701
15°	4973	1315
25°	861	466
35°	106	82
45°	10	12
55°	8	7
65°	4	5
75°	4	3
85°	0	1
90°	0	

TEST NUMBER: P1255760

CATALOG NUMBER: P3A24R359035D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7704.8
1°	7702.7
2°	7678.2
3°	7631.3
4°	7588.4
5°	7519.1
6°	7447.7
7°	7368.1
8°	7270.1
9°	7117.1
10°	6915.1
11°	6635.6
12°	6298.9
13°	5899.0
14°	5458.2
15°	4972.6
17.5°	3703.4
20°	2477.1
22.5°	1493.6
25°	861.1
27.5°	514.2
30°	320.4
32.5°	185.7
35°	106.1
37.5°	67.3
40°	40.8
42.5°	20.4
45°	10.2
47.5°	8.2
50°	8.2
52.5°	8.2
55°	8.2
57.5°	6.1
60°	6.1
62.5°	6.1
65°	4.1
67.5°	4.1
70°	4.1
72.5°	4.1
75°	4.1
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P1255760
CATALOG NUMBER: P3A24R359035D010 E3D1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)