

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255864

Luminaire Tested: P3A24R509035D010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1255864  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A24R509035D010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 90CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1506.0 lumens  
Efficiency: N/A  
Efficacy: 52.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255864

CATALOG NUMBER: P3A24R509035D010 E3DLP1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1255864

CATALOG NUMBER: P3A24R509035D010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 82  | 78  | 85  | 80  | 77  |  | 83  | 79  | 76  |  | 81  |
| 5   | 91  | 83  | 76  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  |  | 78  | 74  | 70  |  | 77  |
| 6   | 87  | 77  | 71  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 72  |
| 7   | 82  | 73  | 67  | 62  | 81  | 72  | 66  | 62  | 71  | 66  | 62  |  | 70  | 65  | 61  |  | 68  |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 64  | 59  | 55  | 63  | 58  | 55  |  | 63  | 58  | 54  |  | 62  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 438013 |
| 5°  | 426237 |
| 10° | 393023 |
| 15° | 345655 |
| 20° | 289195 |
| 25° | 229320 |
| 30° | 168254 |
| 35° | 115670 |
| 40° | 73509  |
| 45° | 41090  |
| 50° | 22242  |
| 55° | 18695  |
| 60° | 16095  |
| 65° | 14788  |
| 70° | 13079  |
| 75° | 12115  |
| 80° | 10355  |
| 85° | 10315  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 41090 cd/sqm

TEST NUMBER: P1255864

CATALOG NUMBER: P3A24R509035D010 E3DLP1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 179.4  | 11.9      |
| 10°-20°   | 421.7  | 28.0      |
| 20°-30°   | 431.3  | 28.6      |
| 30°-40°   | 273.5  | 18.2      |
| 40°-50°   | 108.8  | 7.2       |
| 50°-60°   | 44.1   | 2.9       |
| 60°-70°   | 28.2   | 1.9       |
| 70°-80°   | 14.5   | 1.0       |
| 80°-90°   | 4.4    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1032.4 | 68.6      |
| 0°-40°    | 1305.9 | 86.7      |
| 0°-60°    | 1458.8 | 96.9      |
| 0°-90°    | 1506.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1506.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1998 |      |
| 5°  | 1936 | 179  |
| 15° | 1523 | 422  |
| 25° | 948  | 431  |
| 35° | 432  | 274  |
| 45° | 132  | 109  |
| 55° | 49   | 44   |
| 65° | 28   | 28   |
| 75° | 14   | 15   |
| 85° | 4    | 4    |
| 90° | 0    |      |

TEST NUMBER: P1255864

CATALOG NUMBER: P3A24R509035D010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1997.5 |
| 2.5°  | 1983.2 |
| 5°    | 1936.4 |
| 7.5°  | 1863.0 |
| 10°   | 1765.1 |
| 12.5° | 1649.0 |
| 15°   | 1522.6 |
| 17.5° | 1384.0 |
| 20°   | 1239.3 |
| 22.5° | 1094.6 |
| 25°   | 947.8  |
| 27.5° | 801.0  |
| 30°   | 664.5  |
| 32.5° | 542.2  |
| 35°   | 432.1  |
| 37.5° | 338.4  |
| 40°   | 256.8  |
| 42.5° | 189.6  |
| 45°   | 132.5  |
| 47.5° | 89.7   |
| 50°   | 65.2   |
| 52.5° | 55.0   |
| 55°   | 48.9   |
| 57.5° | 42.8   |
| 60°   | 36.7   |
| 62.5° | 32.6   |
| 65°   | 28.5   |
| 67.5° | 24.5   |
| 70°   | 20.4   |
| 72.5° | 16.3   |
| 75°   | 14.3   |
| 77.5° | 10.2   |
| 80°   | 8.2    |
| 82.5° | 6.1    |
| 85°   | 4.1    |
| 87.5° | 2.0    |
| 90°   | 0.0    |

(END OF REPORT)