

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255910

Luminaire Tested: P3A24R609035D010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1255910  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A24R609035D010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 90CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2146.0 lumens  
Efficiency: N/A  
Efficacy: 74.5 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255910

CATALOG NUMBER: P3A24R609035D010 E3DL1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1255910

CATALOG NUMBER: P3A24R609035D010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 94  | 93  |    |    |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |    |    |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 84  | 91  | 86  | 83  | 88  | 85  | 82  | 86  | 83  | 80  | 79  |    |    |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 81  | 77  | 85  | 80  | 76  | 83  | 79  | 75  | 81  | 77  | 75  | 73  |    |    |
| 5   | 91  | 82  | 76  | 71  | 89  | 81  | 75  | 71  | 79  | 74  | 70  | 78  | 73  | 70  | 76  | 72  | 69  | 68  |    |    |
| 6   | 86  | 77  | 70  | 66  | 84  | 76  | 70  | 66  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 63  |    |    |
| 7   | 82  | 72  | 66  | 61  | 80  | 71  | 65  | 61  | 70  | 65  | 61  | 69  | 64  | 60  | 68  | 63  | 60  | 59  |    |    |
| 8   | 77  | 68  | 61  | 57  | 76  | 67  | 61  | 57  | 66  | 60  | 57  | 65  | 60  | 56  | 64  | 59  | 56  | 55  |    |    |
| 9   | 74  | 64  | 57  | 53  | 72  | 63  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  |    |    |
| 10  | 70  | 60  | 54  | 50  | 69  | 60  | 54  | 50  | 59  | 53  | 50  | 58  | 53  | 50  | 57  | 53  | 49  | 48  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 506736 |
| 5°  | 501936 |
| 10° | 487299 |
| 15° | 456552 |
| 20° | 404098 |
| 25° | 338052 |
| 30° | 264927 |
| 35° | 192203 |
| 40° | 127868 |
| 45° | 79698  |
| 50° | 43154  |
| 55° | 12463  |
| 60° | 11622  |
| 65° | 10585  |
| 70° | 10450  |
| 75° | 10336  |
| 80° | 10355  |
| 85° | 10315  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 79698 cd/sqm

TEST NUMBER: P1255910

CATALOG NUMBER: P3A24R609035D010 E3DL1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 214.7  | 10.0      |
| 10°-20°   | 558.0  | 26.0      |
| 20°-30°   | 636.0  | 29.6      |
| 30°-40°   | 451.0  | 21.0      |
| 40°-50°   | 204.6  | 9.5       |
| 50°-60°   | 43.4   | 2.0       |
| 60°-70°   | 20.9   | 1.0       |
| 70°-80°   | 12.9   | 0.6       |
| 80°-90°   | 4.4    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1408.7 | 65.6      |
| 0°-40°    | 1859.7 | 86.7      |
| 0°-60°    | 2107.7 | 98.2      |
| 0°-90°    | 2146.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2146.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2311 |      |
| 5°  | 2280 | 215  |
| 15° | 2011 | 558  |
| 25° | 1397 | 636  |
| 35° | 718  | 451  |
| 45° | 257  | 205  |
| 55° | 33   | 43   |
| 65° | 20   | 21   |
| 75° | 12   | 13   |
| 85° | 4    | 4    |
| 90° | 0    |      |



TEST NUMBER: P1255910

CATALOG NUMBER: P3A24R609035D010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2310.9 |
| 2.5°  | 2302.8 |
| 5°    | 2280.3 |
| 7.5°  | 2241.6 |
| 10°   | 2188.5 |
| 12.5° | 2113.1 |
| 15°   | 2011.1 |
| 17.5° | 1882.6 |
| 20°   | 1731.7 |
| 22.5° | 1568.5 |
| 25°   | 1397.2 |
| 27.5° | 1221.7 |
| 30°   | 1046.3 |
| 32.5° | 879.1  |
| 35°   | 718.0  |
| 37.5° | 575.2  |
| 40°   | 446.7  |
| 42.5° | 338.6  |
| 45°   | 257.0  |
| 47.5° | 191.7  |
| 50°   | 126.5  |
| 52.5° | 59.1   |
| 55°   | 32.6   |
| 57.5° | 28.6   |
| 60°   | 26.5   |
| 62.5° | 24.5   |
| 65°   | 20.4   |
| 67.5° | 18.4   |
| 70°   | 16.3   |
| 72.5° | 14.3   |
| 75°   | 12.2   |
| 77.5° | 10.2   |
| 80°   | 8.2    |
| 82.5° | 6.1    |
| 85°   | 4.1    |
| 87.5° | 2.0    |
| 90°   | 0.0    |

(END OF REPORT)