

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426977

Luminaire Tested: P3A24RH9035D010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24RH9035D010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 979.0 lumens
Efficiency: N/A
Efficacy: 34.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426977

CATALOG NUMBER: P3A24RH9035D010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426977

CATALOG NUMBER: P3A24RH9035D010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	472089
5°	432532
10°	377949
15°	331557
20°	167781
25°	83521
30°	75505
35°	57420
40°	40333
45°	27228
50°	17432
55°	11699
60°	8070
65°	6382
70°	3911
75°	3474
80°	2526
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27228 cd/sqm

TEST NUMBER: P1426977

CATALOG NUMBER: P3A24RH9035D010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.9	18.3
10°-20°	370.1	37.8
20°-30°	180.5	18.4
30°-40°	134.8	13.8
40°-50°	69.4	7.1
50°-60°	28.6	2.9
60°-70°	11.6	1.2
70°-80°	4.3	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.4	74.5
0°-40°	864.3	88.3
0°-60°	962.3	98.3
0°-90°	979.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	979.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2153	
5°	1965	179
15°	1460	370
25°	345	180
35°	214	135
45°	88	69
55°	31	29
65°	12	12
75°	4	4
85°	0	1
90°	0	

TEST NUMBER: P1426977

CATALOG NUMBER: P3A24RH9035D010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2152.9
2.5°	2103.9
5°	1965.0
7.5°	1815.9
10°	1697.4
12.5°	1609.6
15°	1460.5
17.5°	1139.8
20°	719.0
22.5°	426.9
25°	345.2
27.5°	318.7
30°	298.2
32.5°	261.5
35°	214.5
37.5°	175.7
40°	140.9
42.5°	112.3
45°	87.8
47.5°	67.4
50°	51.1
52.5°	38.8
55°	30.6
57.5°	24.5
60°	18.4
62.5°	14.3
65°	12.3
67.5°	8.2
70°	6.1
72.5°	6.1
75°	4.1
77.5°	2.0
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)