

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426978

Luminaire Tested: P3A24RH9035D010 E3HY1WMH

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426978
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24RH9035D010 E3HY1WMH
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 90CRI , E3HY1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1247.0 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426978

CATALOG NUMBER: P3A24RH9035D010 E3HY1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1426978

CATALOG NUMBER: P3A24RH9035D010 E3HY1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	104	100	98	100	98	96		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87
5	96	89	84	81	95	88	84	80	87	83	79		85	82	79		84
6	93	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	69	65	73	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	623283
5°	565044
10°	489325
15°	444702
20°	248078
25°	154025
30°	123487
35°	67191
40°	33863
45°	15195
50°	4878
55°	765
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15195 cd/sqm

TEST NUMBER: P1426978

CATALOG NUMBER: P3A24RH9035D010 E3HY1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.9	18.7
10°-20°	496.5	39.8
20°-30°	305.4	24.5
30°-40°	166.7	13.4
40°-50°	41.8	3.3
50°-60°	3.8	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1034.8	83.0
0°-40°	1201.5	96.3
0°-60°	1247.0	100.0
0°-90°	1247.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1247.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2842	
5°	2567	233
15°	1959	496
25°	637	305
35°	251	167
45°	49	42
55°	2	4
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426978

CATALOG NUMBER: P3A24RH9035D010 E3HY1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2842.4
2.5°	2771.0
5°	2567.0
7.5°	2350.7
10°	2197.6
12.5°	2081.3
15°	1958.9
17.5°	1558.9
20°	1063.1
22.5°	712.1
25°	636.6
27.5°	569.3
30°	487.7
32.5°	365.3
35°	251.0
37.5°	171.4
40°	118.3
42.5°	79.6
45°	49.0
47.5°	26.5
50°	14.3
52.5°	6.1
55°	2.0
57.5°	2.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)