

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426017

Luminaire Tested: P3A02RH9027DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426017
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02RH9027DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 2700K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 109.0 lumens
Efficiency: N/A
Efficacy: 30.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426017

CATALOG NUMBER: P3A02RH9027DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426017

CATALOG NUMBER: P3A02RH9027DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52562
5°	48162
10°	42083
15°	36913
20°	18692
25°	9291
30°	8406
35°	6398
40°	4494
45°	3039
50°	1944
55°	1300
60°	877
65°	726
70°	449
75°	424
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3039 cd/sqm

TEST NUMBER: P1426017

CATALOG NUMBER: P3A02RH9027DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.9	18.3
10°-20°	41.2	37.8
20°-30°	20.1	18.4
30°-40°	15.0	13.8
40°-50°	7.7	7.1
50°-60°	3.2	2.9
60°-70°	1.3	1.2
70°-80°	0.5	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	81.2	74.5
0°-40°	96.2	88.3
0°-60°	107.1	98.3
0°-90°	109.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	109.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	240	
5°	219	20
15°	163	41
25°	38	20
35°	24	15
45°	10	8
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426017

CATALOG NUMBER: P3A02RH9027DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	239.7
2.5°	234.2
5°	218.8
7.5°	202.2
10°	189.0
12.5°	179.2
15°	162.6
17.5°	126.9
20°	80.1
22.5°	47.5
25°	38.4
27.5°	35.5
30°	33.2
32.5°	29.1
35°	23.9
37.5°	19.6
40°	15.7
42.5°	12.5
45°	9.8
47.5°	7.5
50°	5.7
52.5°	4.3
55°	3.4
57.5°	2.7
60°	2.0
62.5°	1.6
65°	1.4
67.5°	0.9
70°	0.7
72.5°	0.7
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)