

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426885

Luminaire Tested: P3A20RH9030D010 E3HY1H

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426885
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20RH9030D010 E3HY1H
Description: 3in Adjustable LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1105.0 lumens
Efficiency: N/A
Efficacy: 38.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426885

CATALOG NUMBER: P3A20RH9030D010 E3HY1H

Luminous Intensity Polar Plot



TEST NUMBER: P1426885

CATALOG NUMBER: P3A20RH9030D010 E3HY1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	103		102	101	99		98
2	109	105	102	99	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	84	79	76	91	84	79	75	82	78	75		81	77	74		80
7	88	80	75	72	87	80	75	71	79	74	71		77	74	71		76
8	85	77	71	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	67	64		71	67	64		70
10	79	70	65	62	78	70	65	62	69	65	61		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	489215
5°	460245
10°	423439
15°	383793
20°	223459
25°	146283
30°	118018
35°	58330
40°	29484
45°	13087
50°	3446
55°	650
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13087 cd/sqm

TEST NUMBER: P1426885

CATALOG NUMBER: P3A20RH9030D010 E3HY1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.4	17.5
10°-20°	432.6	39.1
20°-30°	288.4	26.1
30°-40°	152.3	13.8
40°-50°	35.8	3.2
50°-60°	2.6	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.4	82.7
0°-40°	1066.6	96.5
0°-60°	1105.0	100.0
0°-90°	1105.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1105.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2231	
5°	2091	193
15°	1691	433
25°	605	288
35°	218	152
45°	42	36
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426885

CATALOG NUMBER: P3A20RH9030D010 E3HY1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2231.0
2.5°	2195.6
5°	2090.9
7.5°	1981.1
10°	1901.7
12.5°	1815.6
15°	1690.6
17.5°	1357.9
20°	957.6
22.5°	687.4
25°	604.6
27.5°	537.1
30°	466.1
32.5°	347.9
35°	217.9
37.5°	148.6
40°	103.0
42.5°	67.6
45°	42.2
47.5°	23.6
50°	10.1
52.5°	5.1
55°	1.7
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)