

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426887

Luminaire Tested: P3A20RH9030D010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20RH9030D010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 811.1 lumens
Efficiency: N/A
Efficacy: 28.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426887

CATALOG NUMBER: P3A20RH9030D010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426887

CATALOG NUMBER: P3A20RH9030D010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	391087
5°	358309
10°	313087
15°	274667
20°	138985
25°	69198
30°	62541
35°	47569
40°	33434
45°	22576
50°	14430
55°	9711
60°	6666
65°	5292
70°	3270
75°	2881
80°	2147
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22576 cd/sqm

TEST NUMBER: P1426887

CATALOG NUMBER: P3A20RH9030D010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.2	18.3
10°-20°	306.6	37.8
20°-30°	149.5	18.4
30°-40°	111.7	13.8
40°-50°	57.5	7.1
50°-60°	23.7	2.9
60°-70°	9.6	1.2
70°-80°	3.6	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	604.3	74.5
0°-40°	716.0	88.3
0°-60°	797.2	98.3
0°-90°	811.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	811.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1784	
5°	1628	148
15°	1210	307
25°	286	150
35°	178	112
45°	73	58
55°	25	24
65°	10	10
75°	3	4
85°	0	1
90°	0	

TEST NUMBER: P1426887

CATALOG NUMBER: P3A20RH9030D010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1783.5
2.5°	1742.9
5°	1627.8
7.5°	1504.3
10°	1406.1
12.5°	1333.4
15°	1209.9
17.5°	944.2
20°	595.6
22.5°	353.7
25°	286.0
27.5°	264.0
30°	247.0
32.5°	216.6
35°	177.7
37.5°	145.5
40°	116.8
42.5°	93.1
45°	72.8
47.5°	55.8
50°	42.3
52.5°	32.2
55°	25.4
57.5°	20.3
60°	15.2
62.5°	11.8
65°	10.2
67.5°	6.8
70°	5.1
72.5°	5.1
75°	3.4
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)