

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252954

Luminaire Tested: P3A24R159030D010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R159030D010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1631.0 lumens
Efficiency: N/A
Efficacy: 56.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252954

CATALOG NUMBER: P3A24R159030D010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1252954

CATALOG NUMBER: P3A24R159030D010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	116	114	113	111	114	112	111	110	108	107	106		105	104	103		101
2	113	110	108	106	111	109	107	105	106	104	103		103	102	100		100
3	111	107	104	102	109	106	103	101	104	101	100		101	100	98		99
4	109	104	101	99	107	103	101	99	102	99	98		100	98	97		98
5	107	102	99	97	105	101	99	96	100	97	96		99	96	95		97
6	105	100	97	95	104	100	97	95	98	96	94		97	95	93		96
7	103	98	95	93	102	98	95	93	97	94	93		96	94	92		95
8	101	97	94	92	101	96	94	92	96	93	91		95	93	91		94
9	100	95	92	90	99	95	92	90	94	92	90		94	91	90		93
10	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3438869
5°	2981568
10°	1449695
15°	309264
20°	64989
25°	19356
30°	4178
35°	750
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1252954

CATALOG NUMBER: P3A24R159030D010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1058.1	64.9
10°-20°	526.1	32.3
20°-30°	43.9	2.7
30°-40°	2.9	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1628.1	99.8
0°-40°	1631.0	100.0
0°-60°	1631.0	100.0
0°-90°	1631.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1631.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15682	
5°	13545	###
15°	1362	526
25°	80	44
35°	3	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1252954

CATALOG NUMBER: P3A24R159030D010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	15682.5
2.5°	15133.7
5°	13545.3
7.5°	10371.3
10°	6510.7
12.5°	3132.6
15°	1362.3
17.5°	694.9
20°	278.5
22.5°	137.9
25°	80.0
27.5°	41.4
30°	16.5
32.5°	5.5
35°	2.8
37.5°	2.8
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2508-518-2

Test Date: 09/10/2025

Luminaire Tested: LD3A24R159030D010 E3D1LI

Data in this report applies to families of products including LD3A24R159030D010 E3D1LI

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2508-518-2
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/16/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A24R159030D010 E3D1LI**
 Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM

Spectral Parameters

CCT (K): 3028
 CIE u' : 0.2491
 CIE v' : 0.5229
 Duv: 0.0015
 CIE x: 0.4371
 CIE y: 0.4078
 CIE z: 0.1551
 Peak Wavelength (nm): 630
 Dominant Wavelength (nm): 582
 Purity: 53.60472
 R_f: 90.8
 R_g: 98.9

CRI (Ra): 91.6
 R1: 92.4
 R2: 94.8
 R3: 96.1
 R4: 93.3
 R5: 91.7
 R6: 94.8
 R7: 91.4
 R8: 78.7
 R9: 48.5
 R10: 86.1
 R11: 94.5
 R12: 79.7
 R13: 92.8
 R14: 96.7
 R15: 86.9



Test Conditions

Stabilization Time: 65M
 Operation Time: 2H 5M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2508-518-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2508-518-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2508-518-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.4

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.69

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

TM-30-18

Summary

$R_f = 90.8$
 $R_g = 98.9$
 $\text{CIE } R_a = 91.6$
 $R_9 = 48.5$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 99	CES76 = 88
CES02 = 63	CES27 = 95	CES52 = 98	CES77 = 86
CES03 = 32	CES28 = 95	CES53 = 96	CES78 = 86
CES04 = 70	CES29 = 93	CES54 = 96	CES79 = 90
CES05 = 50	CES30 = 98	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 94	CES56 = 94	CES81 = 72
CES07 = 43	CES32 = 86	CES57 = 94	CES82 = 96
CES08 = 42	CES33 = 96	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 93	CES59 = 97	CES84 = 95
CES10 = 76	CES35 = 96	CES60 = 95	CES85 = 80
CES11 = 58	CES36 = 88	CES61 = 94	CES86 = 76
CES12 = 65	CES37 = 94	CES62 = 92	CES87 = 92
CES13 = 44	CES38 = 95	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 82
CES15 = 72	CES40 = 96	CES65 = 87	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 82
CES17 = 50	CES42 = 93	CES67 = 88	CES92 = 76
CES18 = 57	CES43 = 93	CES68 = 90	CES93 = 85
CES19 = 72	CES44 = 99	CES69 = 92	CES94 = 71
CES20 = 67	CES45 = 96	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 95	CES71 = 85	CES96 = 91
CES22 = 79	CES47 = 90	CES72 = 95	CES97 = 94
CES23 = 92	CES48 = 93	CES73 = 84	CES98 = 93
CES24 = 91	CES49 = 94	CES74 = 91	CES99 = 89
CES25 = 72	CES50 = 99	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)