Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled data based on original data using

LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253235

Luminaire Tested: P3A24R659030D010 E3DLD1LI

Issue Date: 1/30/2026

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

Test Information

Test Method:	LM-79-2019
Report Number:	P1253235
	TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab:	INNOVATION CENTER
Issue Date:	1/30/2026
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	IRiS
Catalog Number:	P3A24R659030D010 E3DLD1LI
Description:	3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source:	-
Ballast/Driver:	-

Summary

Lumens per Lamp:	N/A
Luminaire Lumens:	1504.0 lumens
Efficiency:	N/A
Efficacy:	52.2 lumens/watt
Spacing Criteria (0/90/45):	0.94 / 0.94 / 1
Luminous Opening:	Circular (Dia: 0.25' x H: 0')
CIE Type:	Direct

Input Watts (W):	28.8
Input Voltage (V):	NR
Input Current (Ain):	NR
Voltage Rise (V):	NR
Power Factor:	NR
Total Harmonic Distortion (THDi):	NR
Frequency (hertz):	60
Stabilization Time:	NR
Operation Time:	NR
Ambient Temperature (°C):	NR
Test Distance:	24 FT

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1253235
CATALOG NUMBER: P3A24R659030D010 E3DLD1LI

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1253235
CATALOG NUMBER: P3A24R659030D010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267654
5°	264032
10°	255195
15°	240660
20°	221966
25°	201496
30°	178458
35°	151862
40°	120826
45°	85311
50°	49534
55°	27029
60°	25130
65°	22778
70°	20837
75°	19402
80°	16921
85°	14341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 85311 cd/sqm

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1253235
CATALOG NUMBER: P3A24R659030D010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.8	7.5
10°-20°	296.6	19.7
20°-30°	381.2	25.3
30°-40°	352.6	23.4
40°-50°	212.9	14.2
50°-60°	72.6	4.8
60°-70°	43.7	2.9
70°-80°	24.7	1.6
80°-90°	7.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.6	52.6
0°-40°	1143.1	76.0
0°-60°	1428.6	95.0
0°-90°	1504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1504.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1221	
5°	1200	113
15°	1060	297
25°	833	381
35°	567	353
45°	275	213
55°	71	73
65°	44	44
75°	23	25
85°	6	7
90°	0	

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report

TEST NUMBER: P1253235
CATALOG NUMBER: P3A24R659030D010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1220.6
2.5°	1214.8
5°	1199.5
7.5°	1176.6
10°	1146.1
12.5°	1107.9
15°	1060.1
17.5°	1008.5
20°	951.2
22.5°	892.0
25°	832.8
27.5°	769.8
30°	704.8
32.5°	639.9
35°	567.3
37.5°	496.6
40°	422.1
42.5°	347.6
45°	275.1
47.5°	208.2
50°	145.2
52.5°	91.7
55°	70.7
57.5°	63.0
60°	57.3
62.5°	49.7
65°	43.9
67.5°	38.2
70°	32.5
72.5°	28.7
75°	22.9
77.5°	19.1
80°	13.4
82.5°	9.6
85°	5.7
87.5°	3.8
90°	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2508-518-2

Test Date: 09/10/2025

Luminaire Tested: LD3A24R159030D010 E3D1LI

Data in this report applies to families of products including LD3A24R159030D010 E3D1LI

Report Generated By FNC07603 / LDUCLS01DT446
Version: v7.04

Test Information

Test Method:	LM-79-2019
Report Number:	SP1-2508-518-2
Test Lab:	COOPER LIGHTING SOLUTIONS
Photometer:	SP1 - 76IN SPHERE
Measurement Geometry:	4π
Issue Date:	09/16/2025
Manufacturer:	COOPER LIGHTING SOLUTIONS
Product Line:	IRiS
Catalog Number:	**LD3A24R159030D010 E3D1LI**
Description:	3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3D1LI TRIM

Spectral Parameters

CCT (K):	3028	CRI (Ra):	91.6		
CIE u':	0.2491	R1:	92.4	R9:	48.5
CIE v':	0.5229	R2:	94.8	R10:	86.1
Duv:	0.0015	R3:	96.1	R11:	94.5
CIE x:	0.4371	R4:	93.3	R12:	79.7
CIE y:	0.4078	R5:	91.7	R13:	92.8
CIE z:	0.1551	R6:	94.8	R14:	96.7
Peak Wavelength (nm):	630	R7:	91.4	R15:	86.9
Dominant Wavelength (nm):	582	R8:	78.7		
Purity:	53.60472				
Rf:	90.8				
Rg:	98.9				



Test Conditions

Stabilization Time:	65M
Operation Time:	2H 5M
Sphere Temperature (°C):	25.1

REPORT NUMBER: SP1-2508-518-2

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2508-518-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



CCT = 3028K
CIE x = 0.4371
CIE y = 0.4078
Duv = 0.0015

Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2508-518-2

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR **S/P: 1.4**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR **M/P: 2.69**

λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)	λ (nm)	Power W^/nm	Lumens (ϕ/nm)
360	0	NR	490	115	NR	620	398	NR	750	11	NR	880	0	NR
365	0	NR	495	138	NR	625	392	NR	755	10	NR	885	0	NR
370	0	NR	500	165	NR	630	1000	NR	760	9	NR	890	0	NR
375	0	NR	505	190	NR	635	751	NR	765	7	NR	895	0	NR
380	0	NR	510	212	NR	640	261	NR	770	6	NR	900	0	NR
385	0	NR	515	230	NR	645	243	NR	775	5	NR	905	0	NR
390	1	NR	520	242	NR	650	220	NR	780	5	NR	910	0	NR
395	1	NR	525	253	NR	655	183	NR	785	4	NR	915	0	NR
400	2	NR	530	262	NR	660	155	NR	790	4	NR	920	0	NR
405	3	NR	535	270	NR	665	132	NR	795	3	NR	925	0	NR
410	6	NR	540	279	NR	670	121	NR	800	3	NR	930	0	NR
415	10	NR	545	287	NR	675	101	NR	805	2	NR	935	0	NR
420	18	NR	550	296	NR	680	88	NR	810	2	NR	940	0	NR
425	30	NR	555	307	NR	685	76	NR	815	2	NR	945	0	NR
430	48	NR	560	317	NR	690	66	NR	820	2	NR	950	0	NR
435	73	NR	565	327	NR	695	57	NR	825	1	NR	955	0	NR
440	107	NR	570	338	NR	700	49	NR	830	1	NR	960	0	NR
445	147	NR	575	349	NR	705	43	NR	835	1	NR	965	0	NR
450	193	NR	580	361	NR	710	37	NR	840	1	NR	970	0	NR
455	206	NR	585	372	NR	715	32	NR	845	1	NR	975	0	NR
460	170	NR	590	379	NR	720	28	NR	850	1	NR	980	0	NR
465	131	NR	595	380	NR	725	24	NR	855	1	NR	985	0	NR
470	107	NR	600	388	NR	730	20	NR	860	1	NR	990	0	NR
475	94	NR	605	392	NR	735	17	NR	865	1	NR	995	0	NR
480	89	NR	610	451	NR	740	15	NR	870	0	NR	1000	0	NR
485	97	NR	615	511	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2508-518-2

TM-30-18

Summary

R_f = 90.8
R_g = 98.9
CIE R_a = 91.6
R_9 = 48.5

Spectral Power Distribution Comparison



Color Vector Graphics









REPORT NUMBER: SP1-2508-518-2

TM-30-18

Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 91	CES51 = 99	CES76 = 88
CES02 = 63	CES27 = 95	CES52 = 98	CES77 = 86
CES03 = 32	CES28 = 95	CES53 = 96	CES78 = 86
CES04 = 70	CES29 = 93	CES54 = 96	CES79 = 90
CES05 = 50	CES30 = 98	CES55 = 95	CES80 = 92
CES06 = 51	CES31 = 94	CES56 = 94	CES81 = 72
CES07 = 43	CES32 = 86	CES57 = 94	CES82 = 96
CES08 = 42	CES33 = 96	CES58 = 95	CES83 = 94
CES09 = 29	CES34 = 93	CES59 = 97	CES84 = 95
CES10 = 76	CES35 = 96	CES60 = 95	CES85 = 80
CES11 = 58	CES36 = 88	CES61 = 94	CES86 = 76
CES12 = 65	CES37 = 94	CES62 = 92	CES87 = 92
CES13 = 44	CES38 = 95	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 82
CES15 = 72	CES40 = 96	CES65 = 87	CES90 = 96
CES16 = 48	CES41 = 96	CES66 = 89	CES91 = 82
CES17 = 50	CES42 = 93	CES67 = 88	CES92 = 76
CES18 = 57	CES43 = 93	CES68 = 90	CES93 = 85
CES19 = 72	CES44 = 99	CES69 = 92	CES94 = 71
CES20 = 67	CES45 = 96	CES70 = 88	CES95 = 84
CES21 = 86	CES46 = 95	CES71 = 85	CES96 = 91
CES22 = 79	CES47 = 90	CES72 = 95	CES97 = 94
CES23 = 92	CES48 = 93	CES73 = 84	CES98 = 93
CES24 = 91	CES49 = 94	CES74 = 91	CES99 = 89
CES25 = 72	CES50 = 99	CES75 = 86	



REPORT NUMBER: SP1-2508-518-2

TM-30-18

Color Rendition by Hue-Angle Bin







REPORT NUMBER: SP1-2508-518-2

TM-30-18

Measure Comparisons





(END OF REPORT)