

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251599

Luminaire Tested: P3A09R359030DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251599
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A09R359030DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 849.0 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251599

CATALOG NUMBER: P3A09R359030DE010 E3PH1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1251599

CATALOG NUMBER: P3A09R359030DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93	92	91
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90	89	87
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87	85	83
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	82	80
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	79	77
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	78	76	74
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	75	73	71
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	73	71	69
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	71	69	67

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	613372	613372	613372
5°	602838	601539	600263
10°	552473	535884	522858
15°	395598	382999	378345
20°	183439	189763	196414
25°	43527	61915	64576
30°	12787	14635	16484
35°	2945	4711	4310
40°	630	1260	830
45°	217	217	217
50°	239	0	239
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 252 cd/sqm

TEST NUMBER: P1251599

CATALOG NUMBER: P3A09R359030DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.1	29.6
10°-20°	448.9	52.9
20°-30°	135.1	15.9
30°-40°	12.9	1.5
40°-50°	0.9	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	835.1	98.4
0°-40°	848.1	99.9
0°-60°	849.0	100.0
0°-90°	849.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	849.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2797	2797	2797	2797	2797	
5°	2739	2738	2733	2729	2727	254
15°	1743	1730	1687	1680	1667	460
25°	180	198	256	267	267	116
35°	11	15	18	19	16	10
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1251599

CATALOG NUMBER: P3A09R359030DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2797.2	2797.2	2797.2	2797.2	2797.2
1°	2795.7	2795.7	2794.2	2794.2	2791.3
2°	2789.1	2789.8	2786.9	2786.2	2784.0
3°	2778.9	2776.7	2776.7	2775.2	2773.8
4°	2762.8	2758.4	2756.9	2757.7	2754.7
5°	2738.7	2737.9	2732.8	2729.2	2727.0
6°	2712.3	2707.2	2696.2	2686.7	2684.5
7°	2672.8	2661.9	2652.4	2632.6	2629.7
8°	2624.6	2607.0	2586.6	2558.8	2557.3
9°	2565.3	2536.8	2508.3	2471.0	2457.8
10°	2481.2	2454.9	2406.7	2373.7	2348.2
11°	2376.7	2343.8	2287.5	2248.0	2226.8
12°	2258.2	2227.5	2161.7	2125.8	2095.9
13°	2106.1	2080.5	2019.1	1979.6	1956.2
14°	1929.9	1910.8	1852.3	1834.8	1826.7
15°	1742.6	1729.5	1687.1	1679.8	1666.6
17.5°	1282.7	1260.7	1236.6	1241.0	1245.4
20°	786.1	816.8	813.2	829.3	841.7
22.5°	392.0	431.5	477.5	505.3	519.2
25°	179.9	198.2	255.9	266.9	266.9
27.5°	90.7	95.1	120.7	122.9	128.7
30°	50.5	54.1	57.8	64.4	65.1
32.5°	25.6	30.0	31.4	35.1	33.6
35°	11.0	14.6	17.6	19.0	16.1
37.5°	5.1	6.6	9.5	8.8	6.6
40°	2.2	2.9	4.4	3.7	2.9
42.5°	1.5	1.5	2.2	1.5	1.5
45°	0.7	0.7	0.7	0.7	0.7
47.5°	0.7	0.7	0.0	0.7	0.7
50°	0.7	0.0	0.0	0.0	0.7
52.5°	0.7	0.0	0.0	0.0	0.7
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1251599
CATALOG NUMBER: P3A09R359030DE010 E3PH1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2504-409-28

Test Date: 05/16/2025

Luminaire Tested: LD3A09R159030D010 E3D1H

Data in this report applies to families of products including LD3A

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2504-409-28
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/06/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A09R159030D010 E3D1H**
 Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI LEDS, E3D1H TRIM

Spectral Parameters

CCT (K): 3032
 CIE u' : 0.2493
 CIE v' : 0.5211
 Duv: 0.0003
 CIE x: 0.4351
 CIE y: 0.4042
 CIE z: 0.1608
 Peak Wavelength (nm): 615
 Dominant Wavelength (nm): 582
 Purity: 51.90029
 R_f: 91.6
 R_g: 98.2

CRI (Ra): 92.8
 R1: 93.5
 R2: 97.3
 R3: 98.7
 R4: 93.9
 R5: 93.6
 R6: 96.7
 R7: 90.3
 R8: 78.4
 R9: 51.3
 R10: 93.2
 R11: 96.4
 R12: 82.1
 R13: 94.8
 R14: 99.6
 R15: 87.6



Test Conditions

Stabilization Time: 40M
 Operation Time: 1H 40M
 Sphere Temperature (°C): 25.1

REPORT NUMBER: SP1-2504-409-28

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	12/16/2024	6/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2504-409-28

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



REPORT NUMBER: SP1-2504-409-28

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	285	NR	620	993	NR	750	55	NR	880	1	NR
365	0	NR	495	338	NR	625	970	NR	755	47	NR	885	1	NR
370	0	NR	500	392	NR	630	942	NR	760	41	NR	890	1	NR
375	0	NR	505	440	NR	635	902	NR	765	35	NR	895	1	NR
380	0	NR	510	478	NR	640	855	NR	770	30	NR	900	1	NR
385	0	NR	515	505	NR	645	800	NR	775	26	NR	905	1	NR
390	0	NR	520	524	NR	650	743	NR	780	22	NR	910	0	NR
395	1	NR	525	539	NR	655	682	NR	785	19	NR	915	0	NR
400	2	NR	530	554	NR	660	621	NR	790	16	NR	920	0	NR
405	3	NR	535	565	NR	665	563	NR	795	14	NR	925	1	NR
410	5	NR	540	581	NR	670	505	NR	800	12	NR	930	0	NR
415	10	NR	545	593	NR	675	451	NR	805	10	NR	935	0	NR
420	17	NR	550	606	NR	680	401	NR	810	9	NR	940	0	NR
425	32	NR	555	623	NR	685	356	NR	815	8	NR	945	0	NR
430	57	NR	560	645	NR	690	313	NR	820	7	NR	950	0	NR
435	103	NR	565	667	NR	695	274	NR	825	6	NR	955	0	NR
440	175	NR	570	699	NR	700	238	NR	830	5	NR	960	0	NR
445	287	NR	575	732	NR	705	208	NR	835	4	NR	965	0	NR
450	460	NR	580	774	NR	710	180	NR	840	4	NR	970	0	NR
455	550	NR	585	816	NR	715	157	NR	845	3	NR	975	0	NR
460	423	NR	590	862	NR	720	136	NR	850	3	NR	980	0	NR
465	309	NR	595	907	NR	725	117	NR	855	2	NR	985	0	NR
470	269	NR	600	943	NR	730	100	NR	860	2	NR	990	0	NR
475	229	NR	605	974	NR	735	86	NR	865	2	NR	995	0	NR
480	214	NR	610	991	NR	740	72	NR	870	2	NR	1000	0	NR
485	241	NR	615	1000	NR	745	62	NR	875	1	NR			

REPORT NUMBER: SP1-2504-409-28

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.44

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	285	NR	620	993	NR	750	55	NR	880	1	NR
365	0	NR	495	338	NR	625	970	NR	755	47	NR	885	1	NR
370	0	NR	500	392	NR	630	942	NR	760	41	NR	890	1	NR
375	0	NR	505	440	NR	635	902	NR	765	35	NR	895	1	NR
380	0	NR	510	478	NR	640	855	NR	770	30	NR	900	1	NR
385	0	NR	515	505	NR	645	800	NR	775	26	NR	905	1	NR
390	0	NR	520	524	NR	650	743	NR	780	22	NR	910	0	NR
395	1	NR	525	539	NR	655	682	NR	785	19	NR	915	0	NR
400	2	NR	530	554	NR	660	621	NR	790	16	NR	920	0	NR
405	3	NR	535	565	NR	665	563	NR	795	14	NR	925	1	NR
410	5	NR	540	581	NR	670	505	NR	800	12	NR	930	0	NR
415	10	NR	545	593	NR	675	451	NR	805	10	NR	935	0	NR
420	17	NR	550	606	NR	680	401	NR	810	9	NR	940	0	NR
425	32	NR	555	623	NR	685	356	NR	815	8	NR	945	0	NR
430	57	NR	560	645	NR	690	313	NR	820	7	NR	950	0	NR
435	103	NR	565	667	NR	695	274	NR	825	6	NR	955	0	NR
440	175	NR	570	699	NR	700	238	NR	830	5	NR	960	0	NR
445	287	NR	575	732	NR	705	208	NR	835	4	NR	965	0	NR
450	460	NR	580	774	NR	710	180	NR	840	4	NR	970	0	NR
455	550	NR	585	816	NR	715	157	NR	845	3	NR	975	0	NR
460	423	NR	590	862	NR	720	136	NR	850	3	NR	980	0	NR
465	309	NR	595	907	NR	725	117	NR	855	2	NR	985	0	NR
470	269	NR	600	943	NR	730	100	NR	860	2	NR	990	0	NR
475	229	NR	605	974	NR	735	86	NR	865	2	NR	995	0	NR
480	214	NR	610	991	NR	740	72	NR	870	2	NR	1000	0	NR
485	241	NR	615	1000	NR	745	62	NR	875	1	NR			

REPORT NUMBER: SP1-2504-409-28

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.84

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	285	NR	620	993	NR	750	55	NR	880	1	NR
365	0	NR	495	338	NR	625	970	NR	755	47	NR	885	1	NR
370	0	NR	500	392	NR	630	942	NR	760	41	NR	890	1	NR
375	0	NR	505	440	NR	635	902	NR	765	35	NR	895	1	NR
380	0	NR	510	478	NR	640	855	NR	770	30	NR	900	1	NR
385	0	NR	515	505	NR	645	800	NR	775	26	NR	905	1	NR
390	0	NR	520	524	NR	650	743	NR	780	22	NR	910	0	NR
395	1	NR	525	539	NR	655	682	NR	785	19	NR	915	0	NR
400	2	NR	530	554	NR	660	621	NR	790	16	NR	920	0	NR
405	3	NR	535	565	NR	665	563	NR	795	14	NR	925	1	NR
410	5	NR	540	581	NR	670	505	NR	800	12	NR	930	0	NR
415	10	NR	545	593	NR	675	451	NR	805	10	NR	935	0	NR
420	17	NR	550	606	NR	680	401	NR	810	9	NR	940	0	NR
425	32	NR	555	623	NR	685	356	NR	815	8	NR	945	0	NR
430	57	NR	560	645	NR	690	313	NR	820	7	NR	950	0	NR
435	103	NR	565	667	NR	695	274	NR	825	6	NR	955	0	NR
440	175	NR	570	699	NR	700	238	NR	830	5	NR	960	0	NR
445	287	NR	575	732	NR	705	208	NR	835	4	NR	965	0	NR
450	460	NR	580	774	NR	710	180	NR	840	4	NR	970	0	NR
455	550	NR	585	816	NR	715	157	NR	845	3	NR	975	0	NR
460	423	NR	590	862	NR	720	136	NR	850	3	NR	980	0	NR
465	309	NR	595	907	NR	725	117	NR	855	2	NR	985	0	NR
470	269	NR	600	943	NR	730	100	NR	860	2	NR	990	0	NR
475	229	NR	605	974	NR	735	86	NR	865	2	NR	995	0	NR
480	214	NR	610	991	NR	740	72	NR	870	2	NR	1000	0	NR
485	241	NR	615	1000	NR	745	62	NR	875	1	NR			

REPORT NUMBER: SP1-2504-409-28

TM-30-18

Summary

$R_f = 91.6$
 $R_g = 98.2$
 $\text{CIE } R_a = 92.8$
 $R_9 = 51.3$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 96	CES51 = 97	CES76 = 92
CES02 = 63	CES27 = 91	CES52 = 99	CES77 = 88
CES03 = 32	CES28 = 98	CES53 = 98	CES78 = 88
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 91
CES05 = 50	CES30 = 90	CES55 = 91	CES80 = 92
CES06 = 51	CES31 = 97	CES56 = 94	CES81 = 78
CES07 = 43	CES32 = 93	CES57 = 93	CES82 = 96
CES08 = 42	CES33 = 97	CES58 = 94	CES83 = 95
CES09 = 29	CES34 = 97	CES59 = 97	CES84 = 95
CES10 = 76	CES35 = 98	CES60 = 93	CES85 = 80
CES11 = 59	CES36 = 82	CES61 = 93	CES86 = 79
CES12 = 65	CES37 = 98	CES62 = 87	CES87 = 91
CES13 = 44	CES38 = 86	CES63 = 94	CES88 = 95
CES14 = 74	CES39 = 98	CES64 = 92	CES89 = 84
CES15 = 72	CES40 = 97	CES65 = 89	CES90 = 94
CES16 = 48	CES41 = 96	CES66 = 90	CES91 = 77
CES17 = 50	CES42 = 97	CES67 = 89	CES92 = 76
CES18 = 57	CES43 = 96	CES68 = 91	CES93 = 86
CES19 = 72	CES44 = 99	CES69 = 92	CES94 = 76
CES20 = 67	CES45 = 99	CES70 = 89	CES95 = 83
CES21 = 86	CES46 = 96	CES71 = 85	CES96 = 91
CES22 = 79	CES47 = 93	CES72 = 95	CES97 = 96
CES23 = 92	CES48 = 89	CES73 = 85	CES98 = 93
CES24 = 90	CES49 = 97	CES74 = 90	CES99 = 89
CES25 = 72	CES50 = 97	CES75 = 86	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)