

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426545

Luminaire Tested: P3A13RH9035DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426545
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RH9035DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 480.0 lumens
Efficiency: N/A
Efficacy: 32.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426545

CATALOG NUMBER: P3A13RH9035DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426545

CATALOG NUMBER: P3A13RH9035DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231473
5°	212062
10°	185301
15°	162566
20°	82257
25°	40962
30°	37018
35°	28161
40°	19780
45°	13366
50°	8529
55°	5735
60°	3947
65°	3113
70°	1923
75°	1694
80°	1263
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13366 cd/sqm

TEST NUMBER: P1426545

CATALOG NUMBER: P3A13RH9035DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	18.3
10°-20°	181.4	37.8
20°-30°	88.5	18.4
30°-40°	66.1	13.8
40°-50°	34.0	7.1
50°-60°	14.0	2.9
60°-70°	5.7	1.2
70°-80°	2.1	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.6	74.5
0°-40°	423.7	88.3
0°-60°	471.8	98.3
0°-90°	480.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	480.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	963	88
15°	716	181
25°	169	88
35°	105	66
45°	43	34
55°	15	14
65°	6	6
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1426545

CATALOG NUMBER: P3A13RH9035DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1055.6
2.5°	1031.5
5°	963.4
7.5°	890.3
10°	832.2
12.5°	789.2
15°	716.1
17.5°	558.8
20°	352.5
22.5°	209.3
25°	169.3
27.5°	156.2
30°	146.2
32.5°	128.2
35°	105.2
37.5°	86.1
40°	69.1
42.5°	55.1
45°	43.1
47.5°	33.0
50°	25.0
52.5°	19.0
55°	15.0
57.5°	12.0
60°	9.0
62.5°	7.0
65°	6.0
67.5°	4.0
70°	3.0
72.5°	3.0
75°	2.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)