

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255638

Luminaire Tested: P3A24R159035D010 E3D1B

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255638
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R159035D010 E3D1B
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI , E3D1B TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2638.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255638

CATALOG NUMBER: P3A24R159035D010 E3D1B

Luminous Intensity Polar Plot



TEST NUMBER: P1255638

CATALOG NUMBER: P3A24R159035D010 E3D1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	105		104	103	102		101	100	99
2	112	109	107	105		110	108	105	103		105	103	101		102	100	99		99	98	97
3	110	106	102	100		108	104	102	99		102	100	98		100	98	96		98	96	95
4	107	102	99	96		106	101	98	96		99	97	95		98	96	94		96	94	93
5	105	100	96	94		103	99	96	93		97	94	92		96	93	92		94	93	91
6	102	97	94	91		101	96	93	91		95	92	90		94	92	90		93	91	89
7	100	95	91	89		99	94	91	89		93	90	88		92	90	88		91	89	88
8	98	93	89	87		97	92	89	87		91	89	87		91	88	86		90	88	86
9	96	91	88	85		96	91	87	85		90	87	85		89	87	85		89	86	85
10	95	89	86	84		94	89	86	84		88	85	83		88	85	83		87	85	83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5023435
5°	4096269
10°	2006108
15°	614033
20°	260026
25°	117612
30°	45855
35°	21148
40°	6584
45°	2481
50°	1023
55°	382
60°	439
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2481 cd/sqm

TEST NUMBER: P1255638

CATALOG NUMBER: P3A24R159035D010 E3D1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1448.5	54.9
10°-20°	888.8	33.7
20°-30°	238.7	9.1
30°-40°	52.6	2.0
40°-50°	7.4	0.3
50°-60°	1.3	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2576.1	97.7
0°-40°	2628.7	99.6
0°-60°	2637.4	100.0
0°-90°	2638.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2638.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22909	
5°	18609	###
15°	2705	889
25°	486	239
35°	79	53
45°	8	7
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1255638

CATALOG NUMBER: P3A24R159035D010 E3D1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	22908.7
1°	22765.6
2°	22306.5
3°	21479.3
4°	20233.9
5°	18609.4
6°	16771.9
7°	14725.3
8°	12844.8
9°	10851.2
10°	9009.6
11°	7187.1
12°	5529.6
13°	4253.2
14°	3367.0
15°	2704.8
17.5°	1676.5
20°	1114.3
22.5°	750.2
25°	486.1
27.5°	288.1
30°	181.1
32.5°	122.0
35°	79.0
37.5°	44.0
40°	23.0
42.5°	13.0
45°	8.0
47.5°	5.0
50°	3.0
52.5°	2.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P1255638
CATALOG NUMBER: P3A24R159035D010 E3D1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)