

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426749

Luminaire Tested: P3A17RH9050DE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17RH9050DE010 E3HY1MW
Description: 3in Adjustable LED luminaire with, RH optic, 5000K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 675.0 lumens
Efficiency: N/A
Efficacy: 31.8 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426749

CATALOG NUMBER: P3A17RH9050DE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426749

CATALOG NUMBER: P3A17RH9050DE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325500
5°	298216
10°	260583
15°	228605
20°	115673
25°	57584
30°	52059
35°	39592
40°	27824
45°	18793
50°	12008
55°	8067
60°	5570
65°	4410
70°	2693
75°	2372
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18793 cd/sqm

TEST NUMBER: P1426749

CATALOG NUMBER: P3A17RH9050DE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.3	18.3
10°-20°	255.2	37.8
20°-30°	124.4	18.4
30°-40°	93.0	13.8
40°-50°	47.9	7.1
50°-60°	19.7	2.9
60°-70°	8.0	1.2
70°-80°	2.9	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	502.9	74.5
0°-40°	595.9	88.3
0°-60°	663.5	98.3
0°-90°	675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1484	
5°	1355	123
15°	1007	255
25°	238	124
35°	148	93
45°	61	48
55°	21	20
65°	8	8
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1426749

CATALOG NUMBER: P3A17RH9050DE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1484.4
2.5°	1450.6
5°	1354.8
7.5°	1252.0
10°	1170.3
12.5°	1109.8
15°	1007.0
17.5°	785.9
20°	495.7
22.5°	294.3
25°	238.0
27.5°	219.7
30°	205.6
32.5°	180.3
35°	147.9
37.5°	121.1
40°	97.2
42.5°	77.5
45°	60.6
47.5°	46.5
50°	35.2
52.5°	26.8
55°	21.1
57.5°	16.9
60°	12.7
62.5°	9.9
65°	8.5
67.5°	5.6
70°	4.2
72.5°	4.2
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)