

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255818

Luminaire Tested: P3A24R459035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R459035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1118.0 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255818

CATALOG NUMBER: P3A24R459035D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1255818

CATALOG NUMBER: P3A24R459035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	419857
5°	410014
10°	376902
15°	319343
20°	247775
25°	173212
30°	109105
35°	64246
40°	36354
45°	17676
50°	6141
55°	4970
60°	4824
65°	4670
70°	4488
75°	4236
80°	3788
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17676 cd/sqm

TEST NUMBER: P1255818

CATALOG NUMBER: P3A24R459035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.4	15.4
10°-20°	386.3	34.6
20°-30°	328.0	29.3
30°-40°	156.5	14.0
40°-50°	47.1	4.2
50°-60°	11.9	1.1
60°-70°	8.9	0.8
70°-80°	5.3	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.8	79.3
0°-40°	1043.2	93.3
0°-60°	1102.3	98.6
0°-90°	1118.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1118.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1915	
5°	1863	172
15°	1407	386
25°	716	328
35°	240	156
45°	57	47
55°	13	12
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1255818

CATALOG NUMBER: P3A24R459035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1914.7
2.5°	1902.7
5°	1862.7
7.5°	1793.7
10°	1692.7
12.5°	1558.7
15°	1406.7
17.5°	1237.8
20°	1061.8
22.5°	882.8
25°	715.9
27.5°	563.9
30°	430.9
32.5°	323.9
35°	240.0
37.5°	177.0
40°	127.0
42.5°	88.0
45°	57.0
47.5°	32.0
50°	18.0
52.5°	14.0
55°	13.0
57.5°	12.0
60°	11.0
62.5°	10.0
65°	9.0
67.5°	8.0
70°	7.0
72.5°	6.0
75°	5.0
77.5°	4.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)