

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255874

Luminaire Tested: P3A24R559035D010 E3D1WH

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1255874  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A24R559035D010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2633.0 lumens  
Efficiency: N/A  
Efficacy: 91.4 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1255874

CATALOG NUMBER: P3A24R559035D010 E3D1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1255874

CATALOG NUMBER: P3A24R559035D010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 88  |  | 92  | 89  | 87  |  | 90  |
| 4   | 100 | 93  | 88  | 84  | 98  | 92  | 87  | 84  | 90  | 86  | 83  |  | 88  | 84  | 82  |  | 86  |
| 5   | 95  | 88  | 83  | 79  | 94  | 87  | 82  | 78  | 85  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 6   | 91  | 83  | 78  | 74  | 90  | 82  | 77  | 74  | 81  | 76  | 73  |  | 80  | 76  | 73  |  | 78  |
| 7   | 87  | 79  | 73  | 70  | 86  | 78  | 73  | 69  | 77  | 72  | 69  |  | 76  | 72  | 69  |  | 75  |
| 8   | 83  | 75  | 69  | 66  | 82  | 74  | 69  | 66  | 73  | 69  | 65  |  | 72  | 68  | 65  |  | 71  |
| 9   | 80  | 71  | 66  | 62  | 79  | 71  | 66  | 62  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  |
| 10  | 77  | 68  | 62  | 59  | 76  | 67  | 62  | 59  | 67  | 62  | 59  |  | 66  | 62  | 59  |  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 763535 |
| 5°  | 736516 |
| 10° | 762845 |
| 15° | 752104 |
| 20° | 696071 |
| 25° | 562944 |
| 30° | 337368 |
| 35° | 114331 |
| 40° | 31488  |
| 45° | 13955  |
| 50° | 4094   |
| 55° | 765    |
| 60° | 439    |
| 65° | 519    |
| 70° | 641    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13955 cd/sqm

TEST NUMBER: P1255874

CATALOG NUMBER: P3A24R559035D010 E3D1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 323.7  | 12.3      |
| 10°-20°   | 922.4  | 35.0      |
| 20°-30°   | 1025.3 | 38.9      |
| 30°-40°   | 319.2  | 12.1      |
| 40°-50°   | 38.3   | 1.5       |
| 50°-60°   | 2.9    | 0.1       |
| 60°-70°   | 1.0    | 0.0       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 2271.4 | 86.3      |
| 0°-40°    | 2590.6 | 98.4      |
| 0°-60°    | 2631.9 | 100.0     |
| 0°-90°    | 2633.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2633.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3482 |      |
| 5°  | 3346 | 324  |
| 15° | 3313 | 922  |
| 25° | 2327 | 1025 |
| 35° | 427  | 319  |
| 45° | 45   | 38   |
| 55° | 2    | 3    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1255874

CATALOG NUMBER: P3A24R559035D010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3482.0 |
| 1°    | 3469.0 |
| 2°    | 3435.0 |
| 3°    | 3393.0 |
| 4°    | 3355.0 |
| 5°    | 3346.0 |
| 6°    | 3356.0 |
| 7°    | 3377.0 |
| 8°    | 3401.0 |
| 9°    | 3420.0 |
| 10°   | 3426.0 |
| 11°   | 3422.0 |
| 12°   | 3406.0 |
| 13°   | 3381.0 |
| 14°   | 3352.0 |
| 15°   | 3313.0 |
| 16°   | 3268.0 |
| 17°   | 3210.9 |
| 18°   | 3146.9 |
| 19°   | 3069.9 |
| 20°   | 2982.9 |
| 21°   | 2883.8 |
| 22°   | 2766.8 |
| 23°   | 2637.8 |
| 24°   | 2489.7 |
| 25°   | 2326.7 |
| 26°   | 2147.6 |
| 27°   | 1957.6 |
| 28°   | 1754.5 |
| 29°   | 1545.5 |
| 30°   | 1332.4 |
| 31°   | 1118.3 |
| 32°   | 909.3  |
| 32.5° | 816.2  |
| 33°   | 720.2  |
| 34°   | 557.2  |
| 35°   | 427.1  |
| 36°   | 325.1  |
| 37°   | 241.1  |
| 37.5° | 206.1  |
| 38°   | 179.1  |
| 39°   | 136.0  |
| 40°   | 110.0  |
| 42.5° | 70.0   |
| 45°   | 45.0   |



TEST NUMBER: P1255874

CATALOG NUMBER: P3A24R559035D010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 47.5° | 27.0 |
| 50°   | 12.0 |
| 52.5° | 4.0  |
| 55°   | 2.0  |
| 57.5° | 1.0  |
| 60°   | 1.0  |
| 62.5° | 1.0  |
| 65°   | 1.0  |
| 67.5° | 1.0  |
| 70°   | 1.0  |
| 72.5° | 0.0  |
| 75°   | 0.0  |
| 77.5° | 0.0  |
| 80°   | 0.0  |
| 82.5° | 0.0  |
| 85°   | 0.0  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)