

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426987

Luminaire Tested: P3A24RH9050D010 E3HY1H

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426987
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-5)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24RH9050D010 E3HY1H
Description: 3in Adjustable LED luminaire with, RH optic, 5000K CCT AND, 90CRI , E3HY1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1350.0 lumens
Efficiency: N/A
Efficacy: 46.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426987

CATALOG NUMBER: P3A24RH9050D010 E3HY1H

Luminous Intensity Polar Plot



TEST NUMBER: P1426987

CATALOG NUMBER: P3A24RH9050D010 E3HY1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	103		102	101	99		98
2	109	105	102	99	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	84	79	76	91	84	79	75	82	78	75		81	77	74		80
7	88	80	75	72	87	80	75	71	79	74	71		77	74	71		76
8	85	77	71	68	84	76	71	68	75	71	67		74	70	67		73
9	82	73	68	65	81	73	68	65	72	67	64		71	67	64		70
10	79	70	65	62	78	70	65	62	69	65	61		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	597693
5°	562270
10°	517314
15°	468879
20°	273000
25°	178728
30°	144199
35°	71260
40°	36039
45°	16002
50°	4230
55°	803
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16002 cd/sqm

TEST NUMBER: P1426987

CATALOG NUMBER: P3A24RH9050D010 E3HY1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.3	17.5
10°-20°	528.5	39.1
20°-30°	352.3	26.1
30°-40°	186.0	13.8
40°-50°	43.8	3.2
50°-60°	3.1	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1117.1	82.7
0°-40°	1303.1	96.5
0°-60°	1350.0	100.0
0°-90°	1350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1350.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2726	
5°	2554	236
15°	2065	528
25°	739	352
35°	266	186
45°	52	44
55°	2	3
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426987

CATALOG NUMBER: P3A24RH9050D010 E3HY1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	2725.7
2.5°	2682.4
5°	2554.4
7.5°	2420.3
10°	2323.3
12.5°	2218.1
15°	2065.4
17.5°	1658.9
20°	1169.9
22.5°	839.8
25°	738.7
27.5°	656.1
30°	569.5
32.5°	425.1
35°	266.2
37.5°	181.6
40°	125.9
42.5°	82.5
45°	51.6
47.5°	28.9
50°	12.4
52.5°	6.2
55°	2.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)