

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1255876

Luminaire Tested: P3A24R559035D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1255876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A24R559035D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3500K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1090.0 lumens
Efficiency: N/A
Efficacy: 37.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1255876
CATALOG NUMBER: P3A24R559035D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1255876
 CATALOG NUMBER: P3A24R559035D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299296
5°	296257
10°	286100
15°	264474
20°	228220
25°	180252
30°	127868
35°	82449
40°	49521
45°	27910
50°	15010
55°	5352
60°	4824
65°	4670
70°	4488
75°	4236
80°	3788
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27910 cd/sqm



TEST NUMBER: P1255876
 CATALOG NUMBER: P3A24R559035D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	11.6
10°-20°	322.1	29.6
20°-30°	337.6	31.0
30°-40°	197.0	18.1
40°-50°	73.7	6.8
50°-60°	17.3	1.6
60°-70°	8.9	0.8
70°-80°	5.3	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.3	72.1
0°-40°	983.3	90.2
0°-60°	1074.3	98.6
0°-90°	1090.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1090.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1365	
5°	1346	127
15°	1165	322
25°	745	338
35°	308	197
45°	90	74
55°	14	17
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1255876
CATALOG NUMBER: P3A24R559035D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1364.9
2.5°	1360.9
5°	1345.9
7.5°	1321.9
10°	1284.9
12.5°	1232.9
15°	1165.0
17.5°	1079.0
20°	978.0
22.5°	865.0
25°	745.0
27.5°	622.0
30°	505.0
32.5°	399.0
35°	308.0
37.5°	234.0
40°	173.0
42.5°	124.0
45°	90.0
47.5°	65.0
50°	44.0
52.5°	25.0
55°	14.0
57.5°	12.0
60°	11.0
62.5°	10.0
65°	9.0
67.5°	8.0
70°	7.0
72.5°	6.0
75°	5.0
77.5°	4.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

(END OF REPORT)