

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1253720

Luminaire Tested: P3A02R709035DE010 E3LSWW1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1253720
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02R709035DE010 E3LSWW1H
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 90CRI , E3LSWW1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 128.0 lumens
Efficiency: N/A
Efficacy: 35.6 lumens/watt
Spacing Criteria (0/90/45): 1.47 / 0.85 / 1.23
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1253720

CATALOG NUMBER: P3A02R709035DE010 E3LSWW1H

Luminous Intensity Polar Plot



TEST NUMBER: P1253720

CATALOG NUMBER: P3A02R709035DE010 E3LSWW1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	91	91	89
2	103	96	91	86	101	95	89	85	91	87	83	88	85	81	85	82	80	80	80	78
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	70	70	68
4	88	78	70	65	86	77	70	64	74	68	63	72	67	63	70	66	62	62	62	60
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	55	55	53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	49	49	47
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	49	44	44	44	43
8	66	54	46	41	65	53	46	41	52	46	41	51	45	41	50	44	40	40	40	39
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	37	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	34	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	14100	14100	14100	14100	14100
5°	17345	16135	13735	12062	11424
10°	21175	18192	12937	10020	9218
15°	25721	19955	11782	8331	7423
20°	28796	21189	10501	6767	6021
25°	30655	21437	9315	5613	4742
30°	31448	20763	8178	4786	4051
35°	30410	20104	7201	4069	3507
40°	27852	18921	6326	3635	3120
45°	24654	15754	5644	3380	2822
50°	20434	13509	4947	3104	2593
55°	15407	11240	4588	2906	2370
60°	12104	8420	4122	2719	2061
65°	9028	6226	3580	2283	1712
70°	5834	3975	2565	1603	962
75°	2457	2118	1271	593	339
80°	505	505	0	0	0
85°	0	0	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24654 cd/sqm

TEST NUMBER: P1253720

CATALOG NUMBER: P3A02R709035DE010 E3LSWW1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.1	4.8
10°-20°	17.5	13.7
20°-30°	25.7	20.0
30°-40°	28.0	21.8
40°-50°	24.2	18.9
50°-60°	16.2	12.7
60°-70°	8.4	6.5
70°-80°	2.0	1.6
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	49.3	38.5
0°-40°	77.2	60.3
0°-60°	117.6	91.9
0°-90°	128.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	128.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	64	64	64	64	64	
5°	79	73	62	55	52	8
15°	113	88	52	37	33	32
25°	127	89	38	23	20	58
35°	114	75	27	15	13	70
45°	80	51	18	11	9	61
55°	40	29	12	8	6	37
65°	17	12	7	4	3	18
75°	3	2	2	1	0	4
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1253720

CATALOG NUMBER: P3A02R709035DE010 E3LSWW1H

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3
2.5°	71.5	71.2	71.2	70.4	69.7	69.0	67.9	66.8	65.7	64.6	63.9
5°	78.8	79.1	78.8	77.3	75.5	73.3	71.2	68.6	66.1	63.9	62.4
7.5°	87.1	87.1	86.0	84.2	81.7	78.1	74.4	70.1	66.1	62.4	60.6
10°	95.1	95.1	93.3	90.4	86.4	81.7	76.6	70.8	65.3	60.3	58.1
12.5°	104.9	104.6	102.4	97.7	91.8	85.0	78.1	70.8	64.3	58.1	55.2
15°	113.3	112.9	110.0	104.2	96.6	87.9	78.4	70.1	62.1	55.2	51.9
17.5°	119.4	118.7	115.4	109.3	100.6	89.7	78.8	68.6	59.5	51.9	48.6
20°	123.4	123.1	119.4	112.2	102.7	90.8	78.4	66.8	57.0	48.6	45.0
22.5°	126.0	125.2	121.6	113.6	102.7	90.4	77.0	64.3	53.7	45.4	41.7
25°	126.7	126.3	122.0	113.3	101.7	88.6	74.8	61.7	50.5	42.1	38.5
26°	126.7	126.3	122.0	112.9	100.9	87.5	73.7	60.6	49.4	40.7	37.4
27.5°	126.3	126.0	121.3	111.8	99.5	85.7	71.5	58.4	47.2	38.8	35.2
30°	124.2	123.4	118.7	109.3	96.2	82.0	67.9	55.2	43.9	35.6	32.3
32.5°	119.4	118.7	113.6	104.9	92.6	78.1	63.9	51.6	40.7	32.3	29.4
35°	113.6	112.9	107.8	99.5	87.5	75.1	59.5	47.6	37.0	29.8	26.9
37.5°	106.4	105.3	100.9	92.2	81.3	71.9	55.9	43.6	33.8	26.9	24.3
40°	97.3	96.9	92.9	85.0	74.1	66.1	53.7	43.6	30.9	24.3	22.1
42.5°	88.6	87.9	84.2	77.3	67.5	57.7	47.2	41.7	28.7	21.8	20.0
45°	79.5	78.8	75.5	69.7	60.6	50.8	50.8	35.9	24.7	20.0	18.2
47.5°	69.7	69.0	66.4	62.1	54.1	45.4	37.0	29.4	22.5	17.8	16.3
50°	59.9	60.3	58.1	53.7	47.6	39.6	31.9	24.7	19.2	16.0	14.5
52.5°	50.1	49.7	48.3	45.4	41.0	34.1	27.2	21.1	16.7	14.2	13.4
55°	40.3	40.7	39.9	38.1	34.5	29.4	22.9	18.2	14.9	12.7	12.0
57.5°	33.4	33.8	32.3	31.2	28.3	24.0	18.9	15.2	12.7	11.3	10.5
60°	27.6	28.0	26.9	25.4	23.2	19.2	15.2	12.7	11.3	10.2	9.4
62.5°	22.5	22.1	21.4	20.0	18.2	15.2	12.3	10.5	9.4	8.7	8.3
65°	17.4	17.4	16.7	15.6	14.2	12.0	9.8	8.7	8.0	7.3	6.9
67.5°	13.1	13.1	12.3	11.6	10.2	8.7	7.6	6.9	6.5	5.8	5.4
70°	9.1	9.1	8.7	8.3	7.3	6.2	5.8	5.1	4.7	4.4	4.0
72.5°	5.8	5.8	5.8	5.1	4.7	4.0	4.0	3.6	3.3	2.9	2.9
75°	2.9	3.3	2.9	2.9	2.5	2.5	2.2	2.2	1.8	1.8	1.5
77.5°	1.1	1.1	1.1	1.1	1.1	1.1	0.7	0.7	0.7	0.7	0.7
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1253720

CATALOG NUMBER: P3A02R709035DE010 E3LSWW1H

CANDELA DISTRIBUTION (continued):

	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3	64.3
2.5°	63.2	62.1	61.4	60.3	59.5	58.8	58.4	58.1	58.1	58.1
5°	61.4	59.5	57.7	55.9	54.8	53.7	52.6	52.3	51.9	51.9
7.5°	59.2	56.3	53.7	51.6	49.7	48.6	47.6	46.8	46.5	46.5
10°	56.3	52.6	49.7	46.8	45.0	43.6	42.8	41.7	41.7	41.4
12.5°	53.0	48.6	45.4	42.8	41.0	39.2	38.1	37.4	37.0	37.0
15°	49.4	45.0	41.4	38.5	36.7	34.9	33.8	33.0	32.7	32.7
17.5°	45.7	41.0	37.4	34.5	32.7	30.9	29.8	29.0	29.0	28.7
20°	42.1	37.4	33.8	30.9	29.0	27.6	26.5	25.8	25.4	25.8
22.5°	38.8	34.1	30.5	28.0	25.8	24.3	23.2	22.9	22.5	22.5
25°	35.2	30.9	27.6	25.0	23.2	21.8	20.7	20.3	20.0	19.6
26°	34.1	29.8	26.5	24.0	22.1	20.7	20.0	19.2	18.9	18.9
27.5°	32.7	28.0	25.0	22.5	20.7	19.6	18.5	18.2	17.8	17.8
30°	29.4	25.4	22.5	20.3	18.9	17.4	16.7	16.3	16.0	16.0
32.5°	26.9	22.9	20.3	18.5	17.1	16.0	15.2	14.5	14.5	14.5
35°	24.3	20.7	18.5	16.7	15.2	14.2	13.8	13.4	13.1	13.1
37.5°	22.1	18.9	16.7	15.2	14.2	13.1	12.3	12.0	12.0	12.0
40°	20.0	17.4	15.2	13.8	12.7	12.0	11.3	10.9	10.9	10.9
42.5°	18.2	15.6	14.2	12.7	11.6	10.9	10.5	10.2	9.8	9.8
45°	16.7	14.5	12.7	11.6	10.9	10.2	9.4	9.1	9.1	9.1
47.5°	14.9	13.4	11.6	10.5	9.8	9.1	8.7	8.3	8.3	8.3
50°	13.8	12.3	10.9	9.8	9.1	8.3	8.0	7.6	7.6	7.6
52.5°	12.3	11.3	10.2	9.1	8.3	7.6	7.3	6.9	6.9	6.9
55°	11.3	10.2	9.1	8.3	7.6	6.9	6.5	6.2	6.2	6.2
57.5°	10.2	9.1	8.3	7.6	6.9	6.5	5.8	5.8	5.4	5.4
60°	9.1	8.0	7.3	6.9	6.2	5.8	5.1	4.7	4.7	4.7
62.5°	7.6	7.3	6.5	5.8	5.1	4.7	4.4	4.0	4.0	4.0
65°	6.5	6.2	5.4	4.7	4.4	4.0	3.6	3.3	3.3	3.3
67.5°	5.4	4.7	4.4	4.0	3.6	3.3	2.9	2.5	2.2	2.5
70°	4.0	3.6	3.3	2.9	2.5	2.2	1.8	1.8	1.5	1.5
72.5°	2.5	2.2	2.2	1.8	1.5	1.5	1.1	1.1	0.7	0.7
75°	1.5	1.5	1.1	1.1	0.7	0.7	0.4	0.4	0.4	0.4
77.5°	0.7	0.4	0.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

IRiS

Report Number: SP1-2504-409-24

Test Date: 05/15/2025

Luminaire Tested: LD3A17R159035D010 E3D1WH

Data in this report applies to families of products including LD3A

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2504-409-24
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 09/15/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: IRiS
 Catalog Number: **LD3A17R159035D010 E3D1WH**
 Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 90CRI LEDS, E3D1WH TRIM

Spectral Parameters

CCT (K): 3464
 CIE u' : 0.2361
 CIE v' : 0.5136
 Duv: 0.0012
 CIE x: 0.4086
 CIE y: 0.3951
 CIE z: 0.1963
 Peak Wavelength (nm): 614
 Dominant Wavelength (nm): 580
 Purity: 41.2143
 R_f: 91.8
 R_g: 98.4

CRI (Ra): 92.8
 R1: 93.1
 R2: 95.9
 R3: 98.0
 R4: 94.1
 R5: 92.9
 R6: 95.0
 R7: 92.5
 R8: 81.1
 R9: 53.9
 R10: 89.9
 R11: 95.7
 R12: 78.6
 R13: 94.0
 R14: 98.5
 R15: 88.0



Test Conditions

Stabilization Time: 62M
 Operation Time: 2H 2M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP1-2504-409-24

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	76INCH SPHERE IN0058	6/16/2025	12/16/2025
Power Meter	XITRON INXT2011004	1/21/2025	1/21/2026
AC Power Source	CHROMA 61603 IN0063	10/22/2024	10/22/2025
DC Power Source	AGILENT E3634A IN0208	10/22/2024	10/22/2025
Sphere Thermometer	ONSET IN0085	10/22/2024	10/22/2025
Room Thermometer	ONSET IN0046	10/22/2024	10/22/2025

REPORT NUMBER: SP1-2504-409-24

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2504-409-24

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	358	NR	620	985	NR	750	62	NR	880	1	NR
365	0	NR	495	424	NR	625	960	NR	755	53	NR	885	1	NR
370	0	NR	500	486	NR	630	930	NR	760	46	NR	890	1	NR
375	0	NR	505	547	NR	635	889	NR	765	40	NR	895	1	NR
380	0	NR	510	590	NR	640	844	NR	770	34	NR	900	1	NR
385	0	NR	515	623	NR	645	792	NR	775	30	NR	905	1	NR
390	1	NR	520	645	NR	650	738	NR	780	25	NR	910	1	NR
395	2	NR	525	662	NR	655	681	NR	785	22	NR	915	1	NR
400	4	NR	530	671	NR	660	623	NR	790	19	NR	920	1	NR
405	7	NR	535	685	NR	665	568	NR	795	16	NR	925	1	NR
410	12	NR	540	693	NR	670	513	NR	800	14	NR	930	0	NR
415	22	NR	545	704	NR	675	461	NR	805	12	NR	935	0	NR
420	39	NR	550	712	NR	680	414	NR	810	10	NR	940	0	NR
425	70	NR	555	726	NR	685	368	NR	815	9	NR	945	0	NR
430	120	NR	560	740	NR	690	326	NR	820	8	NR	950	0	NR
435	200	NR	565	757	NR	695	288	NR	825	7	NR	955	0	NR
440	315	NR	570	782	NR	700	253	NR	830	6	NR	960	0	NR
445	475	NR	575	809	NR	705	222	NR	835	5	NR	965	0	NR
450	656	NR	580	844	NR	710	194	NR	840	4	NR	970	0	NR
455	697	NR	585	874	NR	715	169	NR	845	4	NR	975	0	NR
460	539	NR	590	911	NR	720	148	NR	850	3	NR	980	0	NR
465	408	NR	595	943	NR	725	128	NR	855	3	NR	985	0	NR
470	341	NR	600	968	NR	730	111	NR	860	2	NR	990	0	NR
475	291	NR	605	988	NR	735	95	NR	865	2	NR	995	0	NR
480	278	NR	610	996	NR	740	81	NR	870	2	NR	1000	0	NR
485	308	NR	615	998	NR	745	70	NR	875	2	NR			

REPORT NUMBER: SP1-2504-409-24

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.6

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	358	NR	620	985	NR	750	62	NR	880	1	NR
365	0	NR	495	424	NR	625	960	NR	755	53	NR	885	1	NR
370	0	NR	500	486	NR	630	930	NR	760	46	NR	890	1	NR
375	0	NR	505	547	NR	635	889	NR	765	40	NR	895	1	NR
380	0	NR	510	590	NR	640	844	NR	770	34	NR	900	1	NR
385	0	NR	515	623	NR	645	792	NR	775	30	NR	905	1	NR
390	1	NR	520	645	NR	650	738	NR	780	25	NR	910	1	NR
395	2	NR	525	662	NR	655	681	NR	785	22	NR	915	1	NR
400	4	NR	530	671	NR	660	623	NR	790	19	NR	920	1	NR
405	7	NR	535	685	NR	665	568	NR	795	16	NR	925	1	NR
410	12	NR	540	693	NR	670	513	NR	800	14	NR	930	0	NR
415	22	NR	545	704	NR	675	461	NR	805	12	NR	935	0	NR
420	39	NR	550	712	NR	680	414	NR	810	10	NR	940	0	NR
425	70	NR	555	726	NR	685	368	NR	815	9	NR	945	0	NR
430	120	NR	560	740	NR	690	326	NR	820	8	NR	950	0	NR
435	200	NR	565	757	NR	695	288	NR	825	7	NR	955	0	NR
440	315	NR	570	782	NR	700	253	NR	830	6	NR	960	0	NR
445	475	NR	575	809	NR	705	222	NR	835	5	NR	965	0	NR
450	656	NR	580	844	NR	710	194	NR	840	4	NR	970	0	NR
455	697	NR	585	874	NR	715	169	NR	845	4	NR	975	0	NR
460	539	NR	590	911	NR	720	148	NR	850	3	NR	980	0	NR
465	408	NR	595	943	NR	725	128	NR	855	3	NR	985	0	NR
470	341	NR	600	968	NR	730	111	NR	860	2	NR	990	0	NR
475	291	NR	605	988	NR	735	95	NR	865	2	NR	995	0	NR
480	278	NR	610	996	NR	740	81	NR	870	2	NR	1000	0	NR
485	308	NR	615	998	NR	745	70	NR	875	2	NR			

REPORT NUMBER: SP1-2504-409-24

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.22

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	358	NR	620	985	NR	750	62	NR	880	1	NR
365	0	NR	495	424	NR	625	960	NR	755	53	NR	885	1	NR
370	0	NR	500	486	NR	630	930	NR	760	46	NR	890	1	NR
375	0	NR	505	547	NR	635	889	NR	765	40	NR	895	1	NR
380	0	NR	510	590	NR	640	844	NR	770	34	NR	900	1	NR
385	0	NR	515	623	NR	645	792	NR	775	30	NR	905	1	NR
390	1	NR	520	645	NR	650	738	NR	780	25	NR	910	1	NR
395	2	NR	525	662	NR	655	681	NR	785	22	NR	915	1	NR
400	4	NR	530	671	NR	660	623	NR	790	19	NR	920	1	NR
405	7	NR	535	685	NR	665	568	NR	795	16	NR	925	1	NR
410	12	NR	540	693	NR	670	513	NR	800	14	NR	930	0	NR
415	22	NR	545	704	NR	675	461	NR	805	12	NR	935	0	NR
420	39	NR	550	712	NR	680	414	NR	810	10	NR	940	0	NR
425	70	NR	555	726	NR	685	368	NR	815	9	NR	945	0	NR
430	120	NR	560	740	NR	690	326	NR	820	8	NR	950	0	NR
435	200	NR	565	757	NR	695	288	NR	825	7	NR	955	0	NR
440	315	NR	570	782	NR	700	253	NR	830	6	NR	960	0	NR
445	475	NR	575	809	NR	705	222	NR	835	5	NR	965	0	NR
450	656	NR	580	844	NR	710	194	NR	840	4	NR	970	0	NR
455	697	NR	585	874	NR	715	169	NR	845	4	NR	975	0	NR
460	539	NR	590	911	NR	720	148	NR	850	3	NR	980	0	NR
465	408	NR	595	943	NR	725	128	NR	855	3	NR	985	0	NR
470	341	NR	600	968	NR	730	111	NR	860	2	NR	990	0	NR
475	291	NR	605	988	NR	735	95	NR	865	2	NR	995	0	NR
480	278	NR	610	996	NR	740	81	NR	870	2	NR	1000	0	NR
485	308	NR	615	998	NR	745	70	NR	875	2	NR			

REPORT NUMBER: SP1-2504-409-24


TM-30-18

Summary

$R_f = 91.8$
 $R_g = 98.4$
 $CIE R_a = 92.8$
 $R_9 = 53.9$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 95	CES51 = 98	CES76 = 89
CES02 = 62	CES27 = 92	CES52 = 99	CES77 = 90
CES03 = 31	CES28 = 97	CES53 = 98	CES78 = 86
CES04 = 70	CES29 = 97	CES54 = 93	CES79 = 94
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 93
CES06 = 51	CES31 = 97	CES56 = 95	CES81 = 84
CES07 = 42	CES32 = 92	CES57 = 94	CES82 = 97
CES08 = 41	CES33 = 99	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 96	CES59 = 97	CES84 = 95
CES10 = 75	CES35 = 97	CES60 = 93	CES85 = 83
CES11 = 58	CES36 = 83	CES61 = 93	CES86 = 83
CES12 = 64	CES37 = 97	CES62 = 88	CES87 = 92
CES13 = 43	CES38 = 88	CES63 = 93	CES88 = 96
CES14 = 74	CES39 = 98	CES64 = 91	CES89 = 86
CES15 = 71	CES40 = 96	CES65 = 88	CES90 = 96
CES16 = 47	CES41 = 97	CES66 = 89	CES91 = 76
CES17 = 49	CES42 = 96	CES67 = 88	CES92 = 78
CES18 = 56	CES43 = 96	CES68 = 90	CES93 = 87
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 78
CES20 = 66	CES45 = 98	CES70 = 88	CES95 = 83
CES21 = 86	CES46 = 97	CES71 = 83	CES96 = 91
CES22 = 78	CES47 = 95	CES72 = 95	CES97 = 96
CES23 = 91	CES48 = 91	CES73 = 83	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 92	CES99 = 90
CES25 = 71	CES50 = 98	CES75 = 84	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)