

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262793

Luminaire Tested: P3A13R509727DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262793  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R509727DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1130.0 lumens  
Efficiency: N/A  
Efficacy: 77.4 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262793  
CATALOG NUMBER: P3A13R509727DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1262793  
 CATALOG NUMBER: P3A13R509727DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	394881
5°	384371
10°	366816
15°	332079
20°	287282
25°	235659
30°	135363
35°	42054
40°	11307
45°	3969
50°	955
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3969 cd/sqm



TEST NUMBER: P1262793  
 CATALOG NUMBER: P3A13R509727DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.6	14.5
10°-20°	405.3	35.9
20°-30°	426.0	37.7
30°-40°	121.9	10.8
40°-50°	11.9	1.1
50°-60°	1.0	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	994.9	88.0
0°-40°	1116.8	98.8
0°-60°	1129.7	100.0
0°-90°	1130.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1130.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1801	
5°	1746	164
15°	1463	405
25°	974	426
35°	157	122
45°	13	12
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1262793  
CATALOG NUMBER: P3A13R509727DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1800.8
1°	1798.1
2°	1790.1
3°	1778.5
4°	1763.0
5°	1746.2
6°	1728.3
7°	1709.1
8°	1691.2
9°	1670.5
10°	1647.4
11°	1620.6
12°	1589.9
13°	1551.7
14°	1510.2
15°	1462.8
16°	1412.5
17°	1363.9
18°	1314.1
19°	1270.2
20°	1231.1
21°	1193.7
22°	1151.0
23°	1102.0
24°	1044.5
25°	974.0
26°	897.4
27°	812.1
28°	727.2
29°	635.5
30°	534.6
31°	440.1
32°	353.2
32.5°	315.4
33°	277.1
34°	212.5
35°	157.1
36°	115.2
37°	85.7
37.5°	74.2
38°	64.2
39°	49.8
40°	39.5
42.5°	22.3
45°	12.8



TEST NUMBER: P1262793  
CATALOG NUMBER: P3A13R509727DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	7.2
50°	2.8
52.5°	1.2
55°	0.8
57.5°	0.8
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)