

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262974

Luminaire Tested: P3A17R209727DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262974
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R209727DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 849.0 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262974
CATALOG NUMBER: P3A17R209727DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1262974
 CATALOG NUMBER: P3A17R209727DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210005
5°	204402
10°	188017
15°	165495
20°	141949
25°	119257
30°	96395
35°	73321
40°	52183
45°	34453
50°	21355
55°	14031
60°	12762
65°	11726
70°	11092
75°	10082
80°	9471
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 34453 cd/sqm



TEST NUMBER: P1262974
 CATALOG NUMBER: P3A17R209727DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	10.1
10°-20°	203.0	23.9
20°-30°	225.3	26.5
30°-40°	171.9	20.2
40°-50°	88.0	10.4
50°-60°	36.2	4.3
60°-70°	22.5	2.7
70°-80°	12.7	1.5
80°-90°	3.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.2	60.6
0°-40°	686.0	80.8
0°-60°	810.2	95.4
0°-90°	849.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	849.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	958	
5°	929	86
15°	729	203
25°	493	225
35°	274	172
45°	111	88
55°	37	36
65°	23	23
75°	12	13
85°	3	4
90°	0	



TEST NUMBER: P1262974
CATALOG NUMBER: P3A17R209727DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	957.7
1°	958.8
2°	954.4
3°	949.1
4°	940.4
5°	928.6
6°	914.5
7°	899.4
8°	883.3
9°	863.9
10°	844.4
12.5°	788.4
15°	729.0
17.5°	668.7
20°	608.3
22.5°	547.9
25°	492.9
27.5°	437.9
30°	380.7
32.5°	326.8
35°	273.9
37.5°	227.6
40°	182.3
42.5°	143.4
45°	111.1
47.5°	84.1
50°	62.6
52.5°	46.4
55°	36.7
57.5°	33.4
60°	29.1
62.5°	25.9
65°	22.6
67.5°	19.4
70°	17.3
72.5°	14.0
75°	11.9
77.5°	9.7
80°	7.5
82.5°	5.4
85°	3.2
87.5°	1.1
90°	0.0

(END OF REPORT)