

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263267

Luminaire Tested: P3A17R709727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263267
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R709727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 775.0 lumens
Efficiency: N/A
Efficacy: 36.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263267

CATALOG NUMBER: P3A17R709727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263267

CATALOG NUMBER: P3A17R709727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181784
5°	178450
10°	168267
15°	152714
20°	133572
25°	112676
30°	92267
35°	71581
40°	51239
45°	32437
50°	16170
55°	9902
60°	8508
65°	7835
70°	6924
75°	6354
80°	5430
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32437 cd/sqm

TEST NUMBER: P1263267

CATALOG NUMBER: P3A17R709727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	9.8
10°-20°	187.2	24.2
20°-30°	213.2	27.5
30°-40°	166.7	21.5
40°-50°	81.9	10.6
50°-60°	25.2	3.2
60°-70°	14.9	1.9
70°-80°	8.0	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	476.0	61.4
0°-40°	642.7	82.9
0°-60°	749.8	96.7
0°-90°	775.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	775.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	829	
5°	811	76
15°	673	187
25°	466	213
35°	267	167
45°	105	82
55°	26	25
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1263267

CATALOG NUMBER: P3A17R709727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	829.0
2.5°	824.7
5°	810.7
7.5°	788.0
10°	755.7
12.5°	718.0
15°	672.7
17.5°	624.2
20°	572.4
22.5°	518.5
25°	465.7
27.5°	414.0
30°	364.4
32.5°	314.8
35°	267.4
37.5°	222.1
40°	179.0
42.5°	139.1
45°	104.6
47.5°	73.3
50°	47.4
52.5°	31.3
55°	25.9
57.5°	22.6
60°	19.4
62.5°	17.2
65°	15.1
67.5°	12.9
70°	10.8
72.5°	8.6
75°	7.5
77.5°	6.5
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)