

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263379

Luminaire Tested: P3A20R259727D010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R259727D010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1136.0 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263379
CATALOG NUMBER: P3A20R259727D010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1263379

CATALOG NUMBER: P3A20R259727D010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	269978
5°	263548
10°	244217
15°	217504
20°	186916
25°	158888
30°	130805
35°	101910
40°	73337
45°	46516
50°	27530
55°	18924
60°	17367
65°	16137
70°	14490
75°	13217
80°	12502
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 46516 cd/sqm



TEST NUMBER: P1263379

CATALOG NUMBER: P3A20R259727D010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	9.8
10°-20°	266.0	23.4
20°-30°	300.5	26.5
30°-40°	237.7	20.9
40°-50°	120.1	10.6
50°-60°	48.1	4.2
60°-70°	30.8	2.7
70°-80°	17.0	1.5
80°-90°	4.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.5	59.6
0°-40°	915.3	80.6
0°-60°	1083.4	95.4
0°-90°	1136.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1136.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1231	
5°	1197	111
15°	958	266
25°	657	301
35°	381	238
45°	150	120
55°	50	48
65°	31	31
75°	16	17
85°	4	5
90°	0	



TEST NUMBER: P1263379

CATALOG NUMBER: P3A20R259727D010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1231.2
1°	1231.2
2°	1227.0
3°	1219.9
4°	1210.0
5°	1197.3
6°	1181.7
7°	1163.3
8°	1143.5
9°	1120.9
10°	1096.8
11°	1069.9
12°	1044.4
13°	1014.7
14°	986.4
15°	958.1
17.5°	878.8
20°	801.0
22.5°	727.4
25°	656.7
27.5°	587.3
30°	516.6
32.5°	450.0
35°	380.7
37.5°	317.0
40°	256.2
42.5°	199.5
45°	150.0
47.5°	111.8
50°	80.7
52.5°	60.9
55°	49.5
57.5°	45.3
60°	39.6
62.5°	35.4
65°	31.1
67.5°	26.9
70°	22.6
72.5°	19.8
75°	15.6
77.5°	12.7
80°	9.9
82.5°	7.1
85°	4.2
87.5°	1.4



TEST NUMBER: P1263379
CATALOG NUMBER: P3A20R259727D010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)