

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263401

Luminaire Tested: P3A20R309727D010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263401
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R309727D010 E3D1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1800.9 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263401
CATALOG NUMBER: P3A20R309727D010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1263401

CATALOG NUMBER: P3A20R309727D010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	96	95	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	92	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	89	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1466615
5°	1438913
10°	1273791
15°	807019
20°	306347
25°	90707
30°	35828
35°	10975
40°	4866
45°	1768
50°	1433
55°	1070
60°	1228
65°	1453
70°	898
75°	1186
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1768 cd/sqm



TEST NUMBER: P1263401
 CATALOG NUMBER: P3A20R309727D010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	600.9	33.4
10°-20°	936.5	52.0
20°-30°	217.5	12.1
30°-40°	33.7	1.9
40°-50°	5.8	0.3
50°-60°	2.7	0.1
60°-70°	2.2	0.1
70°-80°	1.5	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1754.9	97.4
0°-40°	1788.6	99.3
0°-60°	1797.0	99.8
0°-90°	1800.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1800.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6688	
5°	6537	601
15°	3555	937
25°	375	217
35°	41	34
45°	6	6
55°	3	3
65°	3	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1263401
CATALOG NUMBER: P3A20R309727D010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6688.3
1°	6684.1
2°	6665.7
3°	6634.6
4°	6595.0
5°	6537.0
6°	6464.8
7°	6357.3
8°	6210.2
9°	5993.7
10°	5720.7
11°	5368.5
12°	4971.0
13°	4529.6
14°	4044.4
15°	3554.9
17.5°	2325.6
20°	1312.8
22.5°	670.5
25°	374.9
27.5°	230.6
30°	141.5
32.5°	76.4
35°	41.0
37.5°	26.9
40°	17.0
42.5°	9.9
45°	5.7
47.5°	4.2
50°	4.2
52.5°	2.8
55°	2.8
57.5°	2.8
60°	2.8
62.5°	2.8
65°	2.8
67.5°	1.4
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1263401
CATALOG NUMBER: P3A20R309727D010 E3D1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)