

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263462

Luminaire Tested: P3A20R409727D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263462
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R409727D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1981.0 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263462
CATALOG NUMBER: P3A20R409727D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1263462
 CATALOG NUMBER: P3A20R409727D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88			88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85			85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82			82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79			79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76			76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73			73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70			70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1009766
5°	1002485
10°	976223
15°	872037
20°	578227
25°	216617
30°	57958
35°	22647
40°	8130
45°	3876
50°	1194
55°	535
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3876 cd/sqm



TEST NUMBER: P1263462
 CATALOG NUMBER: P3A20R409727D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.8	21.7
10°-20°	1017.8	51.4
20°-30°	461.6	23.3
30°-40°	59.8	3.0
40°-50°	10.3	0.5
50°-60°	1.2	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1909.2	96.4
0°-40°	1969.0	99.4
0°-60°	1980.6	100.0
0°-90°	1981.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1981.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4605	
5°	4554	430
15°	3841	1018
25°	895	462
35°	85	60
45°	12	10
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263462
CATALOG NUMBER: P3A20R409727D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4604.9
1°	4602.1
2°	4595.2
3°	4584.8
4°	4571.6
5°	4554.3
6°	4534.1
7°	4509.2
8°	4478.7
9°	4437.1
10°	4384.3
11°	4322.6
12°	4240.1
13°	4138.2
14°	4005.0
15°	3841.3
16°	3632.6
17°	3394.7
18°	3109.0
19°	2807.3
20°	2477.9
21°	2148.5
22°	1823.9
23°	1500.7
24°	1183.1
25°	895.3
26°	663.0
27°	485.5
28°	364.8
29°	283.6
30°	228.9
31°	189.3
32°	158.1
32.5°	144.2
33°	130.4
34°	106.1
35°	84.6
36°	66.6
37°	52.7
37.5°	47.2
38°	41.6
39°	34.7
40°	28.4
42.5°	18.7
45°	12.5



TEST NUMBER: P1263462
CATALOG NUMBER: P3A20R409727D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	7.6
50°	3.5
52.5°	1.4
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)