

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265006

Luminaire Tested: P3A13R209730DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265006  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R209730DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 902.0 lumens  
Efficiency: N/A  
Efficacy: 61.8 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265006  
CATALOG NUMBER: P3A13R209730DE010 E3DL1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1265006

CATALOG NUMBER: P3A13R209730DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	693979
5°	630837
10°	466235
15°	288424
20°	164701
25°	94022
30°	52742
35°	28697
40°	15715
45°	8652
50°	5049
55°	3670
60°	3421
65°	3165
70°	2821
75°	2965
80°	2147
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8652 cd/sqm



TEST NUMBER: P1265006  
 CATALOG NUMBER: P3A13R209730DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	248.2	27.5
10°-20°	354.3	39.3
20°-30°	184.9	20.5
30°-40°	71.5	7.9
40°-50°	23.2	2.6
50°-60°	9.1	1.0
60°-70°	6.0	0.7
70°-80°	3.6	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	787.4	87.3
0°-40°	858.9	95.2
0°-60°	891.2	98.8
0°-90°	902.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	902.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3165	
5°	2866	248
15°	1270	354
25°	389	185
35°	107	72
45°	28	23
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1265006  
CATALOG NUMBER: P3A13R209730DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3164.8
1°	3158.7
2°	3121.3
3°	3063.8
4°	2974.9
5°	2865.9
6°	2737.0
7°	2594.1
8°	2428.5
9°	2267.3
10°	2093.9
12.5°	1664.3
15°	1270.5
17.5°	950.7
20°	705.8
22.5°	522.8
25°	388.6
27.5°	286.7
30°	208.3
32.5°	150.7
35°	107.2
37.5°	77.6
40°	54.9
42.5°	39.2
45°	27.9
47.5°	20.0
50°	14.8
52.5°	11.3
55°	9.6
57.5°	8.7
60°	7.8
62.5°	7.0
65°	6.1
67.5°	5.2
70°	4.4
72.5°	4.4
75°	3.5
77.5°	2.6
80°	1.7
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)