

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265059

Luminaire Tested: P3A13R309730DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265059
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R309730DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1100.0 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265059

CATALOG NUMBER: P3A13R309730DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265059

CATALOG NUMBER: P3A13R309730DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	875193
5°	863788
10°	754161
15°	479344
20°	189927
25°	63439
30°	29524
35°	13385
40°	5124
45°	2512
50°	716
55°	344
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2512 cd/sqm

TEST NUMBER: P1265059

CATALOG NUMBER: P3A13R309730DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	358.8	32.6
10°-20°	556.4	50.6
20°-30°	143.5	13.0
30°-40°	33.7	3.1
40°-50°	6.6	0.6
50°-60°	0.8	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1058.6	96.2
0°-40°	1092.3	99.3
0°-60°	1099.6	100.0
0°-90°	1100.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1100.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3991	
5°	3924	359
15°	2112	556
25°	262	143
35°	50	34
45°	8	7
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265059

CATALOG NUMBER: P3A13R309730DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3991.2
1°	3988.2
2°	3978.8
3°	3968.1
4°	3952.3
5°	3924.2
6°	3878.5
7°	3802.5
8°	3698.7
9°	3563.3
10°	3387.0
11°	3177.3
12°	2948.5
13°	2685.0
14°	2409.2
15°	2111.5
16°	1819.9
17°	1538.9
18°	1269.5
19°	1022.2
20°	813.9
21°	640.5
22°	503.9
23°	398.8
24°	319.4
25°	262.2
26°	218.6
27°	185.7
28°	160.6
29°	137.5
30°	116.6
32.5°	73.4
35°	50.0
37.5°	31.2
40°	17.9
42.5°	12.0
45°	8.1
47.5°	4.7
50°	2.1
52.5°	0.9
55°	0.9
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P1265059

CATALOG NUMBER: P3A13R309730DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)