

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265110

Luminaire Tested: P3A13R409730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R409730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1224.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265110

CATALOG NUMBER: P3A13R409730DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1265110

CATALOG NUMBER: P3A13R409730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	644466
5°	641359
10°	620474
15°	548948
20°	358151
25°	126878
30°	26916
35°	8861
40°	3235
45°	1085
50°	887
55°	994
60°	746
65°	882
70°	577
75°	763
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 1512 cd/sqm

TEST NUMBER: P1265110

CATALOG NUMBER: P3A13R409730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.2	22.4
10°-20°	638.5	52.2
20°-30°	277.1	22.6
30°-40°	25.5	2.1
40°-50°	3.6	0.3
50°-60°	2.2	0.2
60°-70°	1.6	0.1
70°-80°	1.0	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1189.7	97.2
0°-40°	1215.2	99.3
0°-60°	1221.1	99.8
0°-90°	1224.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1224.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2939	
5°	2914	274
15°	2418	638
25°	524	277
35°	33	26
45°	4	4
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1265110

CATALOG NUMBER: P3A13R409730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2939.0
2.5°	2935.5
5°	2913.7
7.5°	2867.6
10°	2786.6
12.5°	2649.8
15°	2418.1
17.5°	2034.0
20°	1534.8
22.5°	996.5
25°	524.4
27.5°	225.6
30°	106.3
32.5°	57.5
35°	33.1
37.5°	20.0
40°	11.3
42.5°	6.1
45°	3.5
47.5°	2.6
50°	2.6
52.5°	2.6
55°	2.6
57.5°	2.6
60°	1.7
62.5°	1.7
65°	1.7
67.5°	1.7
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)