

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265161

Luminaire Tested: P3A13R459730DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265161
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R459730DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 974.0 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265161
CATALOG NUMBER: P3A13R459730DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265161
 CATALOG NUMBER: P3A13R459730DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88				88
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83				83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78				78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74				74
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	70				70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66				66
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62				62
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59				59
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57				57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	365760
5°	357208
10°	328362
15°	278231
20°	215852
25°	150904
30°	95053
35°	55974
40°	31659
45°	15381
50°	5356
55°	4320
60°	4210
65°	4047
70°	3911
75°	3728
80°	3283
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15381 cd/sqm



TEST NUMBER: P1265161
 CATALOG NUMBER: P3A13R459730DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.2	15.4
10°-20°	336.6	34.6
20°-30°	285.8	29.3
30°-40°	136.3	14.0
40°-50°	41.1	4.2
50°-60°	10.4	1.1
60°-70°	7.8	0.8
70°-80°	4.6	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.6	79.3
0°-40°	908.9	93.3
0°-60°	960.4	98.6
0°-90°	974.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	974.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1668	
5°	1623	150
15°	1226	337
25°	624	286
35°	209	136
45°	50	41
55°	11	10
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1265161
CATALOG NUMBER: P3A13R459730DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1668.0
2.5°	1657.6
5°	1622.8
7.5°	1562.7
10°	1474.7
12.5°	1358.0
15°	1225.6
17.5°	1078.4
20°	925.0
22.5°	769.1
25°	623.7
27.5°	491.3
30°	375.4
32.5°	282.2
35°	209.1
37.5°	154.2
40°	110.6
42.5°	76.7
45°	49.6
47.5°	27.9
50°	15.7
52.5°	12.2
55°	11.3
57.5°	10.5
60°	9.6
62.5°	8.7
65°	7.8
67.5°	7.0
70°	6.1
72.5°	5.2
75°	4.4
77.5°	3.5
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)