

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265332

Luminaire Tested: P3A17R159730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R159730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 711.0 lumens
Efficiency: N/A
Efficacy: 33.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265332
CATALOG NUMBER: P3A17R159730DE010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1265332
 CATALOG NUMBER: P3A17R159730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306598
5°	283380
10°	226226
15°	170898
20°	130141
25°	99175
30°	71049
35°	46364
40°	28425
45°	17180
50°	11428
55°	8831
60°	7587
65°	6590
70°	5898
75°	5846
80°	4420
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17180 cd/sqm



TEST NUMBER: P1265332
 CATALOG NUMBER: P3A17R159730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.0	16.0
10°-20°	210.4	29.6
20°-30°	187.3	26.3
30°-40°	110.8	15.6
40°-50°	45.5	6.4
50°-60°	21.3	3.0
60°-70°	13.0	1.8
70°-80°	6.8	1.0
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.8	72.0
0°-40°	622.6	87.6
0°-60°	689.4	97.0
0°-90°	711.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	711.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1398	
5°	1287	114
15°	753	210
25°	410	187
35°	173	111
45°	55	45
55°	23	21
65°	13	13
75°	7	7
85°	1	2
90°	0	



TEST NUMBER: P1265332
CATALOG NUMBER: P3A17R159730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1398.2
1°	1394.7
2°	1384.3
3°	1363.6
4°	1328.9
5°	1287.4
6°	1242.3
7°	1189.2
8°	1133.8
9°	1077.2
10°	1016.0
12.5°	876.3
15°	752.8
17.5°	646.6
20°	557.7
22.5°	479.2
25°	409.9
27.5°	342.9
30°	280.6
32.5°	224.0
35°	173.2
37.5°	132.8
40°	99.3
42.5°	73.9
45°	55.4
47.5°	42.7
50°	33.5
52.5°	27.7
55°	23.1
57.5°	19.6
60°	17.3
62.5°	15.0
65°	12.7
67.5°	11.5
70°	9.2
72.5°	8.1
75°	6.9
77.5°	4.6
80°	3.5
82.5°	2.3
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)