

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265385

Luminaire Tested: P3A17R259730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R259730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 363.0 lumens
Efficiency: N/A
Efficacy: 17.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265385

CATALOG NUMBER: P3A17R259730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265385

CATALOG NUMBER: P3A17R259730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131788
5°	126436
10°	110753
15°	89036
20°	68396
25°	51753
30°	37398
35°	24842
40°	15057
45°	8776
50°	5595
55°	4549
60°	3991
65°	3528
70°	2885
75°	2881
80°	2147
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8776 cd/sqm

TEST NUMBER: P1265385

CATALOG NUMBER: P3A17R259730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	14.4
10°-20°	108.4	29.9
20°-30°	98.1	27.0
30°-40°	58.9	16.2
40°-50°	23.4	6.4
50°-60°	10.8	3.0
60°-70°	6.6	1.8
70°-80°	3.5	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.8	71.3
0°-40°	317.7	87.5
0°-60°	351.9	96.9
0°-90°	363.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	363.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	601	
5°	574	52
15°	392	108
25°	214	98
35°	93	59
45°	28	23
55°	12	11
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1265385

CATALOG NUMBER: P3A17R259730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	601.0
1°	601.0
2°	598.2
3°	592.0
4°	584.0
5°	574.4
6°	562.0
7°	547.8
8°	531.4
9°	515.0
10°	497.4
11°	477.1
12°	456.1
13°	435.2
14°	414.3
15°	392.2
17.5°	340.1
20°	293.1
22.5°	250.7
25°	213.9
27.5°	179.4
30°	147.7
32.5°	118.8
35°	92.8
37.5°	70.7
40°	52.6
42.5°	38.5
45°	28.3
47.5°	21.5
50°	16.4
52.5°	13.6
55°	11.9
57.5°	10.2
60°	9.1
62.5°	7.4
65°	6.8
67.5°	5.7
70°	4.5
72.5°	4.0
75°	3.4
77.5°	2.8
80°	1.7
82.5°	1.1
85°	1.1
87.5°	0.6



TEST NUMBER: P1265385

CATALOG NUMBER: P3A17R259730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)