

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262565

Luminaire Tested: P3A13R129727DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262565  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R129727DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 763.0 lumens  
Efficiency: N/A  
Efficacy: 49.2 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262565  
CATALOG NUMBER: P3A13R129727DE010 E3DL1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1262565  
 CATALOG NUMBER: P3A13R129727DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93	91	91
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	92	90	88	87
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	651812
5°	578581
10°	401796
15°	237618
20°	135322
25°	77351
30°	42817
35°	22834
40°	12624
45°	6853
50°	4264
55°	3364
60°	2895
65°	2646
70°	2372
75°	2457
80°	1894
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6853 cd/sqm



TEST NUMBER: P1262565  
 CATALOG NUMBER: P3A13R129727DE010 E3DL1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	223.5	29.3
10°-20°	295.0	38.7
20°-30°	151.9	19.9
30°-40°	57.0	7.5
40°-50°	18.7	2.4
50°-60°	8.0	1.1
60°-70°	5.1	0.7
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	670.4	87.9
0°-40°	727.4	95.3
0°-60°	754.1	98.8
0°-90°	763.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2972	
5°	2628	224
15°	1047	295
25°	320	152
35°	85	57
45°	22	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1262565  
CATALOG NUMBER: P3A13R129727DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2972.5
1°	2966.6
2°	2927.6
3°	2853.4
4°	2755.6
5°	2628.5
6°	2484.4
7°	2326.4
8°	2150.7
9°	1977.2
10°	1804.5
12.5°	1388.5
15°	1046.7
17.5°	783.5
20°	579.9
22.5°	432.9
25°	319.7
27.5°	233.0
30°	169.1
32.5°	119.8
35°	85.3
37.5°	61.0
40°	44.1
42.5°	31.6
45°	22.1
47.5°	16.2
50°	12.5
52.5°	10.3
55°	8.8
57.5°	7.4
60°	6.6
62.5°	5.9
65°	5.1
67.5°	4.4
70°	3.7
72.5°	3.7
75°	2.9
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)