

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265463

Luminaire Tested: P3A17R409730DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265463
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R409730DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1617.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265463
CATALOG NUMBER: P3A17R409730DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1265463
 CATALOG NUMBER: P3A17R409730DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88			88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85			85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82			82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79			79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76			76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73			73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70			70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	824232
5°	818268
10°	796846
15°	711809
20°	471981
25°	176817
30°	47298
35°	18498
40°	6641
45°	3163
50°	955
55°	421
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3163 cd/sqm



TEST NUMBER: P1265463
 CATALOG NUMBER: P3A17R409730DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	350.8	21.7
10°-20°	830.8	51.4
20°-30°	376.8	23.3
30°-40°	48.8	3.0
40°-50°	8.4	0.5
50°-60°	1.0	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1558.4	96.4
0°-40°	1607.2	99.4
0°-60°	1616.6	100.0
0°-90°	1617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1617.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3759	
5°	3717	351
15°	3136	831
25°	731	377
35°	69	49
45°	10	8
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1265463
CATALOG NUMBER: P3A17R409730DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3758.8
1°	3756.5
2°	3750.8
3°	3742.3
4°	3731.6
5°	3717.4
6°	3701.0
7°	3680.6
8°	3655.7
9°	3621.8
10°	3578.7
11°	3528.4
12°	3461.0
13°	3377.8
14°	3269.1
15°	3135.5
16°	2965.1
17°	2770.9
18°	2537.7
19°	2291.5
20°	2022.6
21°	1753.7
22°	1488.8
23°	1225.0
24°	965.7
25°	730.8
26°	541.2
27°	396.3
28°	297.8
29°	231.5
30°	186.8
31°	154.5
32°	129.1
32.5°	117.7
33°	106.4
34°	86.6
35°	69.1
36°	54.3
37°	43.0
37.5°	38.5
38°	34.0
39°	28.3
40°	23.2
42.5°	15.3
45°	10.2



TEST NUMBER: P1265463
CATALOG NUMBER: P3A17R409730DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.2
50°	2.8
52.5°	1.1
55°	1.1
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)