

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265482

Luminaire Tested: P3A17R409730DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265482  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R409730DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 848.0 lumens  
Efficiency: N/A  
Efficacy: 40.0 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265482

CATALOG NUMBER: P3A17R409730DE010 E3DLP1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1265482

CATALOG NUMBER: P3A17R409730DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 93  | 97  | 94  | 91  |  | 94  | 92  | 89  |  | 92  |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 86  |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 81  | 76  | 72  |  | 79  | 75  | 71  |  | 77  |
| 6   | 87  | 78  | 72  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 73  |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  |  | 67  | 63  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 264058 |
| 5°  | 258705 |
| 10° | 240877 |
| 15° | 209944 |
| 20° | 169181 |
| 25° | 126806 |
| 30° | 89153  |
| 35° | 58410  |
| 40° | 35352  |
| 45° | 21118  |
| 50° | 12588  |
| 55° | 10169  |
| 60° | 9122   |
| 65° | 7783   |
| 70° | 7373   |
| 75° | 5846   |
| 80° | 5809   |
| 85° | 5787   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21118 cd/sqm

TEST NUMBER: P1265482

CATALOG NUMBER: P3A17R409730DE010 E3DLP1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 109.1  | 12.9      |
| 10°-20°   | 254.7  | 30.0      |
| 20°-30°   | 240.0  | 28.3      |
| 30°-40°   | 138.8  | 16.4      |
| 40°-50°   | 55.3   | 6.5       |
| 50°-60°   | 24.5   | 2.9       |
| 60°-70°   | 15.1   | 1.8       |
| 70°-80°   | 7.9    | 0.9       |
| 80°-90°   | 2.5    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 603.9  | 71.2      |
| 0°-40°    | 742.6  | 87.6      |
| 0°-60°    | 822.4  | 97.0      |
| 0°-90°    | 848.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 848.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1204 |      |
| 5°  | 1175 | 109  |
| 15° | 925  | 255  |
| 25° | 524  | 240  |
| 35° | 218  | 139  |
| 45° | 68   | 55   |
| 55° | 27   | 24   |
| 65° | 15   | 15   |
| 75° | 7    | 8    |
| 85° | 2    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1265482

CATALOG NUMBER: P3A17R409730DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1204.2 |
| 2.5°  | 1197.2 |
| 5°    | 1175.3 |
| 7.5°  | 1134.9 |
| 10°   | 1081.8 |
| 12.5° | 1010.2 |
| 15°   | 924.8  |
| 17.5° | 828.9  |
| 20°   | 725.0  |
| 22.5° | 621.1  |
| 25°   | 524.1  |
| 27.5° | 434.1  |
| 30°   | 352.1  |
| 32.5° | 280.5  |
| 35°   | 218.2  |
| 37.5° | 165.1  |
| 40°   | 123.5  |
| 42.5° | 92.4   |
| 45°   | 68.1   |
| 47.5° | 49.6   |
| 50°   | 36.9   |
| 52.5° | 30.0   |
| 55°   | 26.6   |
| 57.5° | 24.2   |
| 60°   | 20.8   |
| 62.5° | 17.3   |
| 65°   | 15.0   |
| 67.5° | 12.7   |
| 70°   | 11.5   |
| 72.5° | 9.2    |
| 75°   | 6.9    |
| 77.5° | 5.8    |
| 80°   | 4.6    |
| 82.5° | 3.5    |
| 85°   | 2.3    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)