

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265623

Luminaire Tested: P3A17R659730DE010 E3DLP1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265623  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A17R659730DE010 E3DLP1WMH  
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 800.0 lumens  
Efficiency: N/A  
Efficacy: 37.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265623  
CATALOG NUMBER: P3A17R659730DE010 E3DLP1WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P1265623  
 CATALOG NUMBER: P3A17R659730DE010 E3DLP1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85			
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	203339
5°	198283
10°	184655
15°	165472
20°	142929
25°	118870
30°	93736
35°	69466
40°	47861
45°	29677
50°	16136
55°	10131
60°	8596
65°	7783
70°	6668
75°	5846
80°	5809
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29677 cd/sqm



TEST NUMBER: P1265623  
 CATALOG NUMBER: P3A17R659730DE010 E3DLP1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.7	10.5
10°-20°	202.6	25.3
20°-30°	224.0	28.0
30°-40°	162.7	20.3
40°-50°	76.2	9.5
50°-60°	25.7	3.2
60°-70°	14.8	1.9
70°-80°	7.8	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.3	63.8
0°-40°	673.0	84.1
0°-60°	774.9	96.9
0°-90°	800.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	800.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	927	
5°	901	84
15°	729	203
25°	491	224
35°	260	163
45°	96	76
55°	26	26
65°	15	15
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1265623  
CATALOG NUMBER: P3A17R659730DE010 E3DLP1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	927.3
2.5°	921.6
5°	900.8
7.5°	869.7
10°	829.3
12.5°	782.0
15°	728.9
17.5°	671.3
20°	612.5
22.5°	551.3
25°	491.3
27.5°	430.2
30°	370.2
32.5°	312.6
35°	259.5
37.5°	211.1
40°	167.2
42.5°	128.0
45°	95.7
47.5°	69.2
50°	47.3
52.5°	32.3
55°	26.5
57.5°	23.1
60°	19.6
62.5°	17.3
65°	15.0
67.5°	12.7
70°	10.4
72.5°	9.2
75°	6.9
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)