

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262706

Luminaire Tested: P3A13R359727DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R359727DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1033.0 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262706

CATALOG NUMBER: P3A13R359727DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1262706

CATALOG NUMBER: P3A13R359727DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			
3	107	102	98	95	105	101	98	95	98	96	93	96	94	92	94	92	90	89			
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83			
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80			
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78			
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75			
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73			
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	673586
5°	659871
10°	613883
15°	450059
20°	230460
25°	83061
30°	32334
35°	11323
40°	4666
45°	1271
50°	1126
55°	1262
60°	1053
65°	830
70°	1026
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 1356 cd/sqm

TEST NUMBER: P1262706

CATALOG NUMBER: P3A13R359727DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	27.1
10°-20°	524.4	50.8
20°-30°	185.6	18.0
30°-40°	32.5	3.1
40°-50°	4.8	0.5
50°-60°	2.6	0.3
60°-70°	1.9	0.2
70°-80°	1.4	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.5	95.8
0°-40°	1022.0	98.9
0°-60°	1029.4	99.7
0°-90°	1033.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3072	
5°	2998	279
15°	1982	524
25°	343	186
35°	42	32
45°	4	5
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1262706

CATALOG NUMBER: P3A13R359727DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	3071.8
1°	3071.0
2°	3061.2
3°	3042.5
4°	3025.4
5°	2997.8
6°	2969.3
7°	2937.6
8°	2898.5
9°	2837.5
10°	2757.0
11°	2645.5
12°	2511.3
13°	2351.8
14°	2176.1
15°	1982.5
17.5°	1476.5
20°	987.6
22.5°	595.5
25°	343.3
27.5°	205.0
30°	127.7
32.5°	74.0
35°	42.3
37.5°	26.8
40°	16.3
42.5°	8.1
45°	4.1
47.5°	3.3
50°	3.3
52.5°	3.3
55°	3.3
57.5°	2.4
60°	2.4
62.5°	2.4
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P1262706
CATALOG NUMBER: P3A13R359727DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)