

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262722

Luminaire Tested: P3A13R359727DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262722
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R359727DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.0 lumens
Efficiency: N/A
Efficacy: 36.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262722

CATALOG NUMBER: P3A13R359727DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1262722

CATALOG NUMBER: P3A13R359727DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95			93
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87			86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81			80
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76			74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71			69
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66			65
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62			61
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59			57
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55			54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	169723
5°	165529
10°	151322
15°	128446
20°	101696
25°	76916
30°	55983
35°	37878
40°	23272
45°	13366
50°	8051
55°	6537
60°	5701
65°	5085
70°	4167
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13366 cd/sqm

TEST NUMBER: P1262722

CATALOG NUMBER: P3A13R359727DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.5	13.2
10°-20°	156.0	29.5
20°-30°	145.9	27.6
30°-40°	89.3	16.9
40°-50°	35.2	6.7
50°-60°	15.5	2.9
60°-70°	9.6	1.8
70°-80°	5.2	1.0
80°-90°	1.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.4	70.3
0°-40°	460.7	87.3
0°-60°	511.5	96.9
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	752	69
15°	566	156
25°	318	146
35°	142	89
45°	43	35
55°	17	15
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1262722

CATALOG NUMBER: P3A13R359727DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	774.0
1°	774.8
2°	772.3
3°	767.5
4°	760.1
5°	752.0
6°	741.4
7°	729.2
8°	714.6
9°	698.3
10°	679.6
11°	660.1
12°	639.0
13°	616.2
14°	591.0
15°	565.8
17.5°	500.8
20°	435.8
22.5°	373.2
25°	317.9
27.5°	266.7
30°	221.1
32.5°	178.9
35°	141.5
37.5°	108.1
40°	81.3
42.5°	58.5
45°	43.1
47.5°	30.9
50°	23.6
52.5°	19.5
55°	17.1
57.5°	14.6
60°	13.0
62.5°	11.4
65°	9.8
67.5°	8.1
70°	6.5
72.5°	5.7
75°	4.9
77.5°	4.1
80°	3.3
82.5°	2.4
85°	1.6
87.5°	0.8



TEST NUMBER: P1262722
CATALOG NUMBER: P3A13R359727DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)