

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262725

Luminaire Tested: P3A13R359727DE010 E3DLP1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262725  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R359727DE010 E3DLP1WH  
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 855.0 lumens  
Efficiency: N/A  
Efficacy: 58.6 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262725  
CATALOG NUMBER: P3A13R359727DE010 E3DLP1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1262725  
 CATALOG NUMBER: P3A13R359727DE010 E3DLP1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	67
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	431215
5°	414439
10°	361093
15°	276574
20°	185049
25°	111974
30°	64238
35°	35924
40°	19093
45°	9830
50°	4708
55°	3747
60°	3552
65°	2958
70°	3142
75°	2796
80°	3031
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9830 cd/sqm



TEST NUMBER: P1262725  
 CATALOG NUMBER: P3A13R359727DE010 E3DLP1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	171.3	20.0
10°-20°	332.0	38.8
20°-30°	217.3	25.4
30°-40°	88.2	10.3
40°-50°	26.4	3.1
50°-60°	9.0	1.1
60°-70°	6.0	0.7
70°-80°	3.5	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	720.6	84.3
0°-40°	808.8	94.6
0°-60°	844.2	98.7
0°-90°	855.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1966	
5°	1883	171
15°	1218	332
25°	463	217
35°	134	88
45°	32	26
55°	10	9
65°	6	6
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1262725

CATALOG NUMBER: P3A13R359727DE010 E3DLP1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1966.5
1°	1963.3
2°	1954.3
3°	1936.5
4°	1915.3
5°	1882.8
6°	1842.1
7°	1796.6
8°	1745.3
9°	1686.8
10°	1621.7
11°	1549.3
12°	1473.7
13°	1389.1
14°	1308.6
15°	1218.3
17.5°	999.5
20°	793.0
22.5°	610.0
25°	462.8
27.5°	344.8
30°	253.7
32.5°	186.2
35°	134.2
37.5°	95.2
40°	66.7
42.5°	46.4
45°	31.7
47.5°	21.1
50°	13.8
52.5°	10.6
55°	9.8
57.5°	8.9
60°	8.1
62.5°	7.3
65°	5.7
67.5°	4.9
70°	4.9
72.5°	4.1
75°	3.3
77.5°	2.4
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8



TEST NUMBER: P1262725  
CATALOG NUMBER: P3A13R359727DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)