

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265783

Luminaire Tested: P3A20R309730D010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265783  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A20R309730D010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 786.9 lumens  
Efficiency: N/A  
Efficacy: 27.3 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265783  
CATALOG NUMBER: P3A20R309730D010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1265783  
 CATALOG NUMBER: P3A20R309730D010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	95
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	90
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	86
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	82
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82	79	78
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	81	78	76	75
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	79	75	73	71
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	76	72	70	69
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	73	70	67	66
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	71	67	65	63
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	459240
5°	437111
10°	367662
15°	265155
20°	164468
25°	93538
30°	51957
35°	28268
40°	14885
45°	8063
50°	4298
55°	2829
60°	2588
65°	2698
70°	2372
75°	1864
80°	1894
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8063 cd/sqm



TEST NUMBER: P1265783  
 CATALOG NUMBER: P3A20R309730D010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	178.8	22.7
10°-20°	317.8	40.4
20°-30°	183.7	23.3
30°-40°	69.7	8.9
40°-50°	21.4	2.7
50°-60°	7.2	0.9
60°-70°	4.9	0.6
70°-80°	2.6	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.3	86.5
0°-40°	750.1	95.3
0°-60°	778.6	98.9
0°-90°	786.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2094	
5°	1986	179
15°	1168	318
25°	387	184
35°	106	70
45°	26	21
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1265783  
CATALOG NUMBER: P3A20R309730D010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2094.3
1°	2092.8
2°	2080.2
3°	2056.4
4°	2026.6
5°	1985.8
6°	1933.7
7°	1875.7
8°	1811.0
9°	1733.7
10°	1651.2
11°	1562.0
12°	1467.6
13°	1368.7
14°	1268.3
15°	1168.0
17.5°	921.1
20°	704.8
22.5°	522.6
25°	386.6
27.5°	281.0
30°	205.2
32.5°	147.9
35°	105.6
37.5°	73.6
40°	52.0
42.5°	36.4
45°	26.0
47.5°	17.8
50°	12.6
52.5°	8.9
55°	7.4
57.5°	6.7
60°	5.9
62.5°	5.2
65°	5.2
67.5°	4.5
70°	3.7
72.5°	3.0
75°	2.2
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0



TEST NUMBER: P1265783  
CATALOG NUMBER: P3A20R309730D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)