

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265807

Luminaire Tested: P3A20R359730D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R359730D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1924.9 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265807

CATALOG NUMBER: P3A20R359730D010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1265807

CATALOG NUMBER: P3A20R359730D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	103	100		102	100	98		99	98	96		97	95	94
3	107	102	98	95		105	101	97	95		98	96	93		96	94	92		94	92	90
4	104	98	94	91		102	97	93	90		95	92	89		93	90	88		91	89	87
5	100	94	90	87		99	93	89	86		92	88	86		90	87	85		89	86	84
6	97	91	86	83		96	90	86	83		89	85	82		87	84	82		86	83	81
7	94	87	83	80		93	87	83	80		86	82	79		85	81	79		84	81	79
8	91	84	80	77		90	84	80	77		83	79	77		82	79	76		81	78	76
9	89	82	77	74		88	81	77	74		80	77	74		80	76	74		79	76	74
10	86	79	75	72		85	79	75	72		78	74	72		77	74	72		77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1255228
5°	1229647
10°	1143956
15°	838688
20°	429464
25°	154775
30°	60262
35°	21094
40°	8673
45°	2357
50°	2081
55°	2332
60°	1974
65°	1557
70°	1923
75°	2542
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 2542 cd/sqm

TEST NUMBER: P1265807

CATALOG NUMBER: P3A20R359730D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	520.8	27.1
10°-20°	977.1	50.8
20°-30°	345.9	18.0
30°-40°	60.6	3.1
40°-50°	8.9	0.5
50°-60°	4.9	0.3
60°-70°	3.5	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1843.9	95.8
0°-40°	1904.4	98.9
0°-60°	1918.2	99.7
0°-90°	1924.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1924.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5724	
5°	5586	521
15°	3694	977
25°	640	346
35°	79	61
45°	8	9
55°	6	5
65°	3	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1265807

CATALOG NUMBER: P3A20R359730D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	5724.3
1°	5722.8
2°	5704.6
3°	5669.7
4°	5637.9
5°	5586.3
6°	5533.3
7°	5474.2
8°	5401.4
9°	5287.7
10°	5137.6
11°	4929.9
12°	4679.8
13°	4382.7
14°	4055.2
15°	3694.4
17.5°	2751.5
20°	1840.4
22.5°	1109.7
25°	639.7
27.5°	382.0
30°	238.0
32.5°	138.0
35°	78.8
37.5°	50.0
40°	30.3
42.5°	15.2
45°	7.6
47.5°	6.1
50°	6.1
52.5°	6.1
55°	6.1
57.5°	4.5
60°	4.5
62.5°	4.5
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0



TEST NUMBER: P1265807

CATALOG NUMBER: P3A20R359730D010 E3CD1MB

CANDELA DISTRIBUTION (continued):



(END OF REPORT)