

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265808

Luminaire Tested: P3A20R359730D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A20R359730D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1924.9 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265808
CATALOG NUMBER: P3A20R359730D010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1265808
 CATALOG NUMBER: P3A20R359730D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1255228
5°	1229647
10°	1143956
15°	838688
20°	429464
25°	154775
30°	60262
35°	21094
40°	8673
45°	2357
50°	2081
55°	2332
60°	1974
65°	1557
70°	1923
75°	2542
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 2542 cd/sqm



TEST NUMBER: P1265808
 CATALOG NUMBER: P3A20R359730D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	520.8	27.1
10°-20°	977.1	50.8
20°-30°	345.9	18.0
30°-40°	60.6	3.1
40°-50°	8.9	0.5
50°-60°	4.9	0.3
60°-70°	3.5	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1843.9	95.8
0°-40°	1904.4	98.9
0°-60°	1918.2	99.7
0°-90°	1924.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1924.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5724	
5°	5586	521
15°	3694	977
25°	640	346
35°	79	61
45°	8	9
55°	6	5
65°	3	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1265808
CATALOG NUMBER: P3A20R359730D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5724.3
1°	5722.8
2°	5704.6
3°	5669.7
4°	5637.9
5°	5586.3
6°	5533.3
7°	5474.2
8°	5401.4
9°	5287.7
10°	5137.6
11°	4929.9
12°	4679.8
13°	4382.7
14°	4055.2
15°	3694.4
17.5°	2751.5
20°	1840.4
22.5°	1109.7
25°	639.7
27.5°	382.0
30°	238.0
32.5°	138.0
35°	78.8
37.5°	50.0
40°	30.3
42.5°	15.2
45°	7.6
47.5°	6.1
50°	6.1
52.5°	6.1
55°	6.1
57.5°	4.5
60°	4.5
62.5°	4.5
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0



TEST NUMBER: P1265808
CATALOG NUMBER: P3A20R359730D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)